


ELFK SERIES PART NUMBERING SCHEME



- COLOR/PLATING
- 0 = BLACK, TIN-LEAD (STANDARD)
 - 1 = BLACK, SELECTIVE GOLD
 - G = GREEN, TIN-LEAD
 - 1G = GREEN, SEL. GOLD
- MOUNTING EARS
- 0E = BLACK, TIN-LEAD
 - 1E = BLACK, SEL. GOLD
 - GE = GREEN, TIN-LEAD
 - EG = GREEN, SEL. GOLD
- CONSULT PCD FOR PART NO. AND AVAILABILITY OF FOLLOWING OPTIONS:
- * CUSTOM COLORS
 - * CUSTOM MARKING
 - * CUSTOM KEYING
 - * SELECTIVE CONTACT LOADING



RATINGS

CURRENT - 15A
VOLTAGE - 300V
U.L. FILE NO. E83421



RATINGS

CURRENT - PENDING
VOLTAGE - PENDING
CSA FILE NO. LR69703



DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT - PENDING
VOLTAGE - PENDING
TUV FILE NO. 20396



INSTALLATION
RECOMMENDATIONS
WIRE RANGE: AWG #14-26, STRANDED
OR SOLID; AWG #12 STRANDED
WIRE STRIP LENGTH: .310"
TIGHTENING TORQUE: 7 LB-IN.

MATERIALS:
HOUSING: PPO, UL 94 V-0
CONTACT: COPPER ALLOY, NICKEL FINISH
SCREW: STEEL, NICKEL FINISH
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH
MAX OPERATING TEMPERATURE:
105°C

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	SPECIFICATION DRAWING			TITLE ELFK SERIES PLUG ASSEMBLY 45°			
			ENGR	D. MANTER 10-Dec-98		SIZE A	DWG NO.	ELFK02210	REV B
			CHKD						
ORIGINAL STAMPED IN RED	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		J. CAHALY 12/11/98		CODE: 58982	SCALE: NONE	SHEET 1 OF 2		



L- NUM OF POS X CL SPACING



MOUNTING EARS CONFIGURATION

SIZE
A

DWG NO.

ELFK02210

REV

B

CODE: 58982

SCALE: NONE

SHEET 2 OF 2