

3mm

Prism® CBI® Circuit Board Indicator

Surface Mount LED, High Intensity, Round Lens


Dialight

591-2101-0xx

591-2201-0xx

591-2701-0xx

1



U.S. Patent RE 34,254; foreign patents pending.

Part

Number*

Type

591-2101-0xx

AlGaAs Red

591-2201-0xx

High Intensity Green

591-2701-0xx

AlInGaP Yellow

NEW
NEW

Features

- Helps to eliminate mixed technology PC board processing.
- Unique patented low part count design.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase solder processes.
- Packaged on 16mm tape, 7" or 13" reels per EIA-481-2.
- Black housing enhances contrast ratio.
- Housing material meets UL94V-0 flammability rating.
- Lens material meets UL94-HB flammability rating.
- Uses LEDs designed specifically for surface mounting.

*ORDERING INFORMATION

591-2x01-0xx

packaging option →

02	20 pieces on tape
07	7" reel, 400 pcs/reel
13	13" reel, 1600 pcs/reel

NEW

591-2101-0xx
591-2201-0xx
591-2701-0xx

Absolute Maximum Ratings, $T_A=25^{\circ}\text{C}$

Parameter	-2101	-2201	-2701
Color*	21	22	27
Power Dissipation (derate linearly from 25°C $\text{mA}/^{\circ}\text{C}$)	100mA .8	100mA .6	60mA .6
Forward DC Current	200mA	120mA	160mA
Peak Forward Current (10 μ sec)	120mA	120mA	80mA
Operating Temperature	-55°C to $+100^{\circ}\text{C}$		
Storage Temperature	-55°C to $+100^{\circ}\text{C}$		
Soldering Temperatures Convection IR Vapor Phase	235° Peak, above 185° for 90 sec., 215°C for 3 Min.		

Solder Adherence per MIL-STD-202E, Method 208C

*LED colors: 21) AlGaAs Red 22) High Intensity Green, 27) AlInGaP Yellow

U.S. Patent RE 34,254; foreign patents pending.

Operating Characteristics ($T_A = 25^{\circ}\text{C}$)

Parameter	Part No.	Color	Min	Typ	Max	Units	Test Cond.
Forward Voltage V_F	-2101	21		1.8	2.4	V	$I_F = 20\text{mA}$
	-2201	22		2.1	2.6		
	-2701	27		2	2.4		
Reverse Voltage V_R	-2101	21	3	5		V	$I_R = 10\text{mA}$
	-2201	22	5	5			
	-2701	27	5	5			
Dominant Wavelength λ_{Dom}	-2101	21		638		nm	
	-2201	22		569			
	-2701	27		595			
Luminous Intensity I_V	-2101	21		23.9		mcd	$I_F = 10\text{mA}$
	-2201	22		9.1			
	-2701	27		33.6			
Viewing Angle ($2\Theta_{1/2}$)	-2101	21		40		deg.	
	-2201	22		40			
	-2701	27		40			

$\Theta_{1/2}$ is the off axis angle at which the luminous intensity is half the axial luminous intensity

*LED colors: 21) AlGaAs Red 22) High Intensity Green, 27) AlInGaP Yellow

Dialight