







REV.	DATE	DESCRIPTION
NC	09/07/99	INITIAL RELEASE
A	07/21/05	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	07/21/05						
7	HEAT SHRINK TUBE			1		CHECKED								
6	FERRULE	COPPER	GOLD	1		ISSUED				PART DESCRIPTION				
5	HEX NUT	BRASS	GOLD	1		SHEET		1 OF 1		SMB BULKHEAD CRIMP JACK (FOR RG-178B/U, 196A/U CABLE)				
4	LOCK WASHER	BRASS	GOLD	1						PART NO.				
3	CONTACT PIN	BRASS	GOLD	1						142231				
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO.				
1	BODY	BRASS	GOLD	1					1421231.DWG					
DESCRIPTION					MATERIAL	FINISH	QTY	C:/142/142231.DWG		1421231.DWG		REV. A	SIZE A	SCALE NA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142231](#)