






P/N 180580-0004 HOLDER WITHOUT LENS ATTACH FEATURES



ISO TOP VIEW
SCALE 1:1




COB LED
SCALE 1:1

- 1) MATERIALS: COVER: PBT 30% GF, COLOR: WHITE, UL94V-0
HOUSING: PBT 30% GF, COLOR: WHITE, UL94V-0
- 2) WIRE TRAP TERMINALS: COPPER ALLOY
FINISH: LED CONTACT: GOLD OVER NICKEL,
WIRE TRAP: TIN OVER NICKEL.
- 3) APPLICABLE WIRE GAUGE - 18, 20, OR 22 AWG
 - a. SOLID WIRE IS PREFERRED
 - b. PRE-TINNED STRANDED WIRE IS ACCEPTABLE
 - c. 1 cm +2.00/-0.00cm STRIP LENGTH IS RECOMMENDED
- 4) MOUNT HOLDER USING M3 OR 4-40 SCREWS (2),
0.2 NEWTON METER MIN 0.4 NEWTON METER MAX TORQUE





COB MFG.	TYPE	DIM. 'A'	DIM. 'B'	THK.	DIM. 'C' MAX.
NICHIA	L SERIES	19.0	16.0	1.0	14.0

ENTER DESCRIPTION EC NO: SSL2015-0044 DRAWN:GMEYER 2014/11/03 CHKD: GMEYER APPR:GMEYER 2014/12/22	DESCRIPTION	QUALITY SYMBOLS F7=0 F7=0 F7=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
				mm	INCH	DRAWN BY MCOLE	DATE 2013/08/21	TITLE NICHIA LTYPE HOLDER ZHAGA STYLE COVER ASSY						
						CHECKED BY GMEYER	DATE 2014/05/06							
						APPROVED BY		DATE		molex				
B	REV		ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. 1805800004		DOCUMENT NO. SD-180580-004			SHEET NO. 1 OF 3				
					SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

P/N 180580-0005 HOLDER WITH LENS ATTACH FEATURES



ISO VIEW TOP
SCALE 1:1




M3 OR 4-40 TAPPED
HOLES (2)
TORQUE SCREWS 0.2-0.4
NEWTON METERS MAX.

RECOMMENDED MOUNTING DIMENSIONS (NTS)

ENTER DESCRIPTION EC NO: SSL2015-0044 DRAWN: GMEYER CHKD: APPR: GMEYER		DESCRIPTION 2014/11/03 2014/12/22	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 	
				mm INCH	DRAWN BY DATE	TITLE NICHIA LTYPE HOLDER ZHAGA STYLE COVER ASSY					
4 PLACES ± --- ± ---	MCOLE 2013/08/21										
3 PLACES ± --- ± ---	CHECKED BY	DATE	molex								
2 PLACES ± 0.13 ± ---	GMEYER 2014/05/06										
1 PLACE ± 0.25 ± ---	APPROVED BY	DATE	DOCUMENT NO. SD-180580-004								
0 PLACE ± --- ± ---											
ANGULAR ± 1/2°		MATERIAL NO.		SHEET NO.							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		1805800005		2 OF 3							
SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

ILLUSTRATION OF HOLDER WITH LED ATTACHED



ENTER DESCRIPTION EC NO: SSL2015-0044 DRAWN:GMEYER 2014/11/03 CHKD: APPR:GMEYER 2014/12/22	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_B=0 F_C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY MCOLE	DATE 2013/08/21	TITLE NICHIA LTYPE HOLDER ZHAGA STYLE COVER ASSY			
			4 PLACES	± ---	± ---	CHECKED BY	DATE				
			3 PLACES	± ---	± ---	GMEYER	2014/05/06				
			2 PLACES	± 0.13	± ---	APPROVED BY	DATE				
			1 PLACE	± 0.25	± ---	MATERIAL NO. 1805800004				DOCUMENT NO. SD-180580-004	SHEET NO. 3 OF 3
			0 PLACE	± ---	± ---						
ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							