


OMRON®



LR21642



E41515



Pin Type Actuator
No. 6X283

Lever Type Actuator
No. 6X284

Roller Type Actuator
No. 6X285



Plunger Type Actuator
No. 6X286



Roller Plunger
No. 2XC11



Short Roller
No. 2XC12



Cross Roller Plunger
No. 3XG50



Slim Spring Plunger
No. 3XG52



Unidirect Short Roller
Lever No. 3XG53



Short Spring Plunger
No. 3XG30

Snap-Action Switches and Accessories

Functionally interchangeable with Unimax 2HB series.

"Z" SERIES

For general-purpose applications.

- Electrical ratings: SPDT 15 amp @ 125, 250, or 480VAC; 1/2 amp @ 125VDC; 1/4 amp @ 250VDC; 1/8-HP @ 125VAC; 1/4-HP @ 250VAC
- Screw terminals
- Sealed, dripproof (IEC IP62) on No. 3XG49
- 1.00" (25.4mm) center to center on 3.56mm mounting holes

"A" SERIES

For heavy-duty applications.

- Electrical ratings: SPDT 20 amp @ 125, 250, or 480VAC; 10 amp @ 125VAC (Tungsten); 1/2 amp @ 125VDC; 1/4 amp @ 250VDC; 1-HP @ 125VAC; 2-HP @ 250VAC
- Screw terminals
- 1.00" (25.4mm) center to center on 3.56mm mounting holes

Type of Actuator	Overall Dimensions (In.)			Actuator Length (In.)	Operating Force (Oz.)	Movement Differential Travel (In.)	Pretravel (In.)	Overtravel (In.)	Omron Model	Stock No.	Each	Shpg. Wt.
	L	H	D		Make	Release						
"Z" SERIES GENERAL PURPOSE, MAX. VOLTAGE 480VAC, 15A @ 120VAC												
Pin	1.94	0.95	0.69	—	8.8 to 12.3	4.0	0.016	0.005	Z-15G-B7-K	6X283	\$5.58	0.1
Hinge Lever	1.94	1.16	0.69	2.50	2.5	0.5	0.050	0.220	Z-15GW-B7-K	6X284	7.17	0.1
Hinge Lever	1.94	1.16	0.69	2.50	0.99	0.12	0.050	0.394	Z-15GW4-B7-K	3XG54	9.48	0.1
Roller Lever	1.94	1.16	0.69	1.91	3.5	0.79	0.040	0.157	Z-15GW2-B7-K	6X285	9.04	0.1
Panel Mount Plunger	1.94	1.52	0.69	—	8.8 to 12.3	4.0	0.002	0.016	Z-15GQ-B7-K	6X286	8.91	0.1
Panel Mount Roller Plunger	1.94	1.61	0.69	—	8.8 to 12.3	4.0	0.002	0.016	Z-15GQ22-B7-K	2XC11	15.59	0.1
Short Roller	1.94	1.16	0.69	1.05	5.6	1.5	0.020	0.094	Z-15GW22-B7-K	2XC12	8.94	0.1
Short Spring Plunger	1.94	0.95	0.69	—	8.8 to 12.3	4.0	0.002	0.016	Z-15GD-B7-K	3XG48	7.50	0.1
Short Spring Plunger	1.94	0.95	0.69	—	19.1	4.0	0.002	0.071	Z-15GD55-B7-K	3XG49	12.19	0.1
Panel Mount Cross Roller Plunger	1.94	1.61	0.69	—	8.8 to 12.3	4.0	0.002	0.016	Z-15GQ21-B7-K	3XG50	21.04	0.2
Slim Spring Plunger	1.94	0.95	0.69	—	8.8 to 12.3	4.0	0.002	0.016	Z-15GS-B7-K	3XG51	7.86	0.1
Slim Spring Plunger	1.94	0.95	0.69	—	19.1	4.0	0.002	0.075	Z-15GS55-B7-K	3XG52	14.59	0.1
Unidirect Short Roller Lever	1.94	1.16	0.69	1.26	6.0	1.5	0.020	0.094	Z-15GW2277-B7-K	3XG53	10.31	0.1
"A" SERIES HEAVY DUTY, MAX. VOLTAGE 480VAC, 20A @ 120VAC												
Pin	1.94	0.95	0.69	—	14.1 to 22.0	10.0	0.008	0.051	A-20G-B7-K	6X287	7.24	0.1
Hinge Lever	1.94	1.16	0.69	2.50	2.5	0.50	0.094	0.626	A-20GV-B7-K	6X289	7.45	0.1
Roller Lever	1.94	1.16	0.69	1.91	3.2	0.50	0.087	0.472	A-20GV2-B7-K	6X290	9.29	0.1
Panel Mount Plunger	1.94	1.52	0.69	—	14.1 to 22.0	10.0	0.008	0.051	A-20GQ-B7-K	6X288	12.33	0.1
Short Roller	1.94	1.16	0.69	1.03	5.6	1.5	0.047	0.248	A-20GV22-B7-K	2XC10	9.32	0.1
Short Spring Plunger	1.94	0.95	0.69	—	14.1 to 22.0	10.0	0.008	0.051	A-20GD-B7-K	3XG30	11.01	0.1
ACCESSORY										AP-Z	6C920	2.59 0.1
Side Mount, Dustproof PVC Terminal Enclosure, fits Z series above												