



- ACCOMMODATE UNIVERSAL AC SOURCES
- MEET IEC 61000-3-2 HARMONIC CORRECTION
- MEET UNIVERSAL SAFETY STANDARDS
- 19" COMPATIBLE EUROCARD FORMAT
- EMI MEET EN 55022 & FCC CLASS B
- CE MARKING COMPLIANCE
- 3U X 8HP X 160MM FOR VMEbus STANDARD



OUTPUT VOLTAGE / CURRENT RATINGS CHART

SINGLE OUTPUT

MODEL NO.	MAIN VO1 ★@# Typ. Volt.
HPU60-S025180	18.0A 2.5V
HPU60-S033150	15.0A 3.3V
HPU60-S050120	12.0A 5.0V
HPU60-S060100	10.0A 6.0V
HPU60-S120050	5.0A 12.0V
HPU60-S150040	4.0A 15.0V
HPU60-S190030	3.0A 19.0V
HPU60-S240025	2.5A 24.0V
HPU60-S480013	1.3A 48.0V

DUAL OUTPUT

MODEL NO.	MAIN VO1 ★@# Typ. Volt.	AUX. VO2 ▲◇ Typ. Volt.
HPU60-D030E	6.0A 3.0V	6.0A 5.0V
HPU60-D030I	6.0A 3.0V	3.0A 12.0V
HPU60-D050I	5.0A 5.0V	3.0A 12.0V
HPU60-D120I	2.5A 12.0V	2.5A 12.0V
HPU60-D050K	5.0A 5.0V	2.5A 15.0V
HPU60-D150K	2.0A 15.0V	2.0A 15.0V
HPU60-D050M	5.0A 5.0V	1.5A 24.0V
HPU60-D240M	1.4A 24.0V	1.4A 24.0V


TRIPLE OUTPUT

MODEL NO.	MAIN VO1 ★@◇ Typ. Volt.	AUX. VO2 @▲◇ or● Typ. Volt.	AUX. VO3 ●◇ Typ. Volt.
HPU60-T050IE (HPU60-30)	5.0A 5.0V	2.5A 12.0V	1.0A 5.0V
HPU60-T050KK (HPU60-31)	5.0A 5.0V	2.0A 15.0V	0.5A 15.0V
HPU60-T050II (HPU60-32)	5.0A 5.0V	2.5A 12.0V	0.5A 12.0V
HPU60-T030EI	6.0A 3.0V	5.0A 5.0V	1.0A 12.0V
HPU60-T030KK	6.0A 3.0V	2.0A 15.0V	0.5A 15.0V
HPU60-T030II	6.0A 3.0V	2.5A 12.0V	0.5A 12.0V

Symbol: "★" OVP built-in. "@@" Adjustable. "▲" Magnetic Amplifier "●" Installed with Post Regulator.
 "◇" Floating(or isolated)output. "##" Remote sensing.

MECHANICAL DIMENSIONS: MM [INCHES]

WEIGHT: 720.0g (25.40z.)



INPUT & OUTPUT CONNECTORS PIN ASSIGNMENT

	AC INPUT			SINGLE OUTPUT					DUAL OUTPUT					TRIPLE OUTPUT							Status/ Control	
ASSIGNMENT	AC-L	AC-N	AC-G	+VO1	+S	-VO1	-S	NC	+VO1	-VO1	+VO2	-VO2	NC	+VO1	-VO1	+VO2	-VO2	+VO3	-VO3	NC	Log. Inh.	P. Fail
CNTR & Pin#	28	30	32	4,6	8	12,14	10	16,18,24,26	4	6	8	10	12,14,16,18,24,26	4,6	8,10	12	14	16	18	24,26	20	22

Mating connector: DIN 41612-H15 Female