

You are here: Applied Computing & Systems > Display Solutions > ES-1000 LCD Kits > ES-1108N-TVME

ES-1108N-TVME

Email page

8.4" Color TFT-LCD Kit for TTL Interface



Main Features

- LCD Panel: Mitsubishi AA084VC05
- Display: 640 x 480 VGA, 262K
- Viewing Angle (L/R/U/D): 65/65/50/60
- Brightness (nit): 450
- Response Time (ms): 35
- Backlight (hrs.): Replaceable CCFL, 2-tubes, 50,000 hrs
- Operation Temp.: 0 ~ 60 °C
- ES-1108N-TVM-01E ~ 05E LCD Kit Cable Length (mm): 300 (optional)
- Outline Dimensions mm (W x H x D): 199.5 x 149 x 11.5

Datasheet (PDF)

Manual/ Driver/ BIOS/ FAQ

Introduction

8.4" Color TFT-LCD Kit for TTL Interface

Ordering Information	
Part Number	Description
ES-1108N-TVM-01E	8.4" LCD Kit, MTH 450 nites, TTL-01, SVGA
ES-1108N-TVM-02E	8.4" LCD Kit, MTH 450 nites, TTL-02, SVGA
ES-1108N-TVM-03E	8.4" LCD Kit, MTH 450 nites, TTL-03, SVGA
ES-1108N-TVM-04E	8.4" LCD Kit, MTH 450 nites, TTL-04, SVGA
ES-1108N-TVM-05E	8.4" LCD Kit, MTH 450 nites, TTL-05, SVGA
ES-1108N-TVME	8.4" LCD Kit, MTH 450 nites, TTL, SVGA

Contact Information

Office	Phone	Email
--------	-------	-------

Rate this page :

Did the information help you achieve your goal?

☐ Yes ☐ No

* Your eMail address: Your Company

* Your Country:

Afghanistan

Please provide us with comments to help improve this page:

Submit

Live Chat

eCatalog

Whitepaper

- Stimulus Spending Brings Medical Applications to Life: Opportunities and Challenges in Digital Records
- Industrial-Grade Advantech Digital Signage Solutions for Mission-Critical Digital Signage Deployments
- On the Road with Fleet Management
- Advantech Digital Video Solutions: Industrial Strength For 24/7 Operation
- Advantech Medical Computing Enabling Digital Healthcare
- What would you do with a TDP of less than 5 watts?

Services

- Buy Online

Featured Articles

- Panel PC, Flat Panel Computer, Touch Screen, Human Machine Interface
- Industrial Computer
- Fanless PC, Compact PC, Rugged PC, Embedded System, Panel PC