





|                                                      |                                                                                      |
|------------------------------------------------------|--------------------------------------------------------------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 731-639/018-000                                                                      |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 2.5                                                                           |
| Cross section2 (Cross section / AWG)                 | 28 - 12                                                                              |
| Strip length (Strip length / mm)                     | 8 - 9                                                                                |
| Measured voltage (Measured voltage / V)              | 630                                                                                  |
| Measured shock voltage (Measured shock voltage / kV) | 6                                                                                    |
| Pollution degree (Pollution degree)                  | 2                                                                                    |
| Current intensity (Current intensity / A)            | 12                                                                                   |
| RM (PIN SPACING / mm)                                | 7.62                                                                                 |
| P (NO. OF POLES)                                     | 9                                                                                    |
| Height (Height / mm)                                 | 14.3                                                                                 |
| Width (Width / mm)                                   | 69.24                                                                                |
| Depth (Depth / mm)                                   | 27.5                                                                                 |
| No. of connection Points (No. of connection Points)  | 9                                                                                    |
| No. of potentials (No. of potentials)                | 9                                                                                    |
| COLOR (COLOR)                                        | orange                                                                               |
| Comment (Comment)                                    | L = (No. of poles - 1) x Pin Spacing + 8.2 mm  <br>L1 = L - 1.7 mm   L2 = L - 1.2 mm |