

Tyco Part Number: 3 - 1437387 -
6

 Active

RoHS Compliant (Statement of Compliance)

- ? Terminal Block
- ? 12.00 mm Centerline
- ? Number of Circuits = 2
- ? Wire Range = 0.30 - 6.00 ² [22-10] mm [AWG]
- ? With Wire Protection

[View all Features](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

? [12.0 PITCH, W/ WIRE PROTECTOR](#) (PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? Line Drawing

? Tooling

List all Documents

? UL Recognized = File No. E63810

? Screw Plating = Bright Zinc/Chrome

- ? Current Rating (Amps.) = 40
- ? Voltage Rating (VAC) = 250
- ? Wire Protector Material = Stainless Steel

? Centerline (mm [in]) = 12.00 [0.472]
 ? Wire Range (mm [AWG]) = 0.30 -6.00 ² [22-10]
 ? Wire Protection = With
 ? Ground = Without
 ? Series = TSB1000
 ? Flammability Rating = UL 94V -2
 ? CSA File No. = LR28387

- ? Contact Material = Brass
- ? Contact Mating Area Plating = Tin

? Housing Material = Polyamide

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

? Temperature Range (°C) = 105

? Brand = Buchanan