





LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE DWN APVD
J	—	F	REVISED	ECR-08-005781	05MAR'08 J.S S.M
		F1	REVISED PER ECO-10-000444		01FEB10 KK HMR

- 注：
1. 適用製品規格 108-5302
△ 5極ハウジングの回路NO.2と4のコンタクト2本抜き仕様
3. かん合相手製品型番
3.96MM ピッチ2極プラグハウジング：表2参照
リセコンタクト：175151-X (AWG#26-#22)
：175152-X (AWG#20-#16)
△ C寸法は基板穴をパンチ加工する場合、
基板にクラックが発生しない様、寸法設定してください。
△ 4極ハウジングの回路NO.1と3のコンタクト2本抜き仕様
△ 4極ハウジングの回路NO.2と4のコンタクト2本抜き仕様


- NOTES：
1. PRODUCT SPEC 108-5302
△ CIRCUIT NO.2 AND 4 ARE VACANT OF 5POS HOUSING
3. MATING CONN. P/N
3.96MM PITCH 2POS PLUG HSG: SEE TABLE 2
REC CONTACT: 175151-X (AWG#26-#22)
：175152-X (AWG#20-#16)
△ PLEASE DECIDE THE DIMENSION C SO THAT PREVENT CRACKING
OF P.C.B
△ CIRCUIT NO.1 AND 3 ARE VACANT OF 4POS HOUSING
△ CIRCUIT NO.2 AND 4 ARE VACANT OF 4POS HOUSING
△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



178498のみ対象
(APPLIED P/N 178498 ONLY)



断面 "A"- "A"
(SECT)



型番 178498 対象 (APPLIED P/N 178498) 型番 178497 対象 (APPLIED P/N 178497)
178499 対象 (APPLIED P/N 178499)

表1
TABLE1

NO.	名称 (NAME)	材料 (MATERIAL)
①	タブ (TAB)	黄銅 錫めっき (BRASS TIN PLATED)
②	ヘッダーハウジング (HEADER HOUSING)	6/6ナイロンガラス強化 (6/6 NYLON GLASS FILLED)

表 2 (TABLE 2)

ヘッダーアセンブリ P/N (HDR ASS'Y P/N)	極数 (POS.)	適合相手 P/N (MATING CONN. P/N)
178497	4	178481
178498	5	178482
178499	6	178483

基板レイアウト寸法 (P.C.B LAYOUT)
適用基板厚 1.6 (APPLICABLE P.C.B THK 1.6)

SUPERSEDED BY 178497-1		11.88		16.98	3.96MMピッチ4極 (3.96MM PITCH 4POS)	自然色 (NATURAL)	6-178497-1
OBSOLETE △	△	↑	↑	↑	7.92MMピッチ2極 (7.92MM PITCH 2POS)	青 (BLUE)	5-178497-6
	△	11.88	13.58	16.98		赤 (RED)	6-178497-2
	△	↑	↑	↑		自然色 (NATURAL)	5-178497-1
OBSOLETE △	△	↑	↑	↑	3.96MMピッチ 6極 (3.96MM PITCH 6POS)	黒 (BLACK)	178499-9
	△	↑	↑	↑		青 (BLUE)	178499-6
	△	↑	↑	↑		黄色 (YELLOW)	178499-4
OBSOLETE △	△	19.80	21.50	24.90		赤 (RED)	178499-2
	△	↑	↑	↑		自然色 (NATURAL)	178499-1
	△	↑	↑	↑	△ 7.92MMピッチ 3極 (7.92MM PITCH 3POS)	黒 (BLACK)	3-178498-9
OBSOLETE △	△	↑	↑	↑		青 (BLUE)	3-178498-6
	△	↑	↑	↑		黄色 (YELLOW)	3-178498-4
	△	↑	↑	↑		赤 (RED)	3-178498-2
OBSOLETE △	△	15.84	17.54	20.94		自然色 (NATURAL)	3-178498-1
	△	↑	↑	↑	3.96MMピッチ 5極 (3.96MM PITCH 5POS)	黒 (BLACK)	178498-9
	△	↑	↑	↑		青 (BLUE)	178498-6
OBSOLETE △	△	↑	↑	↑		黄色 (YELLOW)	178498-4
	△	↑	↑	↑		赤 (RED)	178498-2
	△	↑	↑	↑		自然色 (NATURAL)	178498-1
OBSOLETE △	△	↑	↑	↑	3.96MMピッチ 4極 (3.96MM PITCH 4POS)	黒 (BLACK)	178497-9
	△	↑	↑	↑		青 (BLUE)	178497-6
	△	↑	↑	↑		黄色 (YELLOW)	178497-4
OBSOLETE △	△	11.88	13.58	16.98		赤 (RED)	178497-2
	△	↑	↑	↑		自然色 (NATURAL)	178497-1
	△	↑	↑	↑	コネクタピッチ及び極数 CONN.PITCH AND POS	ハウジング色調 (COLOR)	型番 (P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN Y.NARISAWA 08MAR'91
CHK N.ONQUE 13MAR'91
APVD Y.FUJITA 13MAR'91

PRODUCT SPEC
製品規格
APPLICATION SPEC
取付適用規格

SEE NOTE 1

MATERIAL 材料
SEE TABLE 1

FINISH 仕上
SEE TABLE 1

WEIGHT
重量

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

AMP UP CONN. 3.96MM PITCH 4-6POS
TAB HEADER ASSY (H TYPE)

SIZE A2 CAGE CODE 00779 DRAWING NO. 178497
RESTRICTED TO

SCALE 1 OF 1 REV F1