

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

SUNON KDE Series

DC Brushless Fan

4010

:40x40x10mm



Model	P/N	Bearing ● VAPO ○ SLEEVE ○ BALL	Rating Voltage (VDC)	Power Current (AMP)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
★ KDE1204PFV1	MS	●	12	0.11	1.3	8200	8.1	0.22	33	16
★ KDE1204PFV2	MS	●	12	0.08	1.0	7000	6.6	0.17	28	16
KDE1204PFS1-8		○	12	0.06	0.7	7000	6.6	0.17	30	16
KDE1204PFS2-8		○	12	0.05	0.6	6000	5.6	0.13	28	16
KDE1204PFS3-8		○	12	0.04	0.5	4500	4.5	0.09	22.8	16
KDE1204PFB1-8		○	12	0.06	0.7	7300	6.9	0.19	30.5	16
KDE1204PFB2-8		○	12	0.05	0.6	6100	6.0	0.14	28.5	16
KDE1204PFB3-8		○	12	0.04	0.5	5300	4.8	0.10	23.5	16
KDE1204PFB1	OC	○	12	0.12	1.4	8400	8.3	0.19	34.4	15.5
KDE1204PFB2	OC	○	12	0.08	1.0	6600	6.5	0.15	27	15.5
KDE1204PFB3	OC	○	12	0.05	0.6	5200	4.7	0.10	24	15.5
KDE1204PFB1	MS	○	12	0.11	1.3	8800	8.6	0.23	37	16
KDE1204PFB2	MS	○	12	0.08	1.0	7600	7.0	0.18	32	16

□

4020

:40x40x20mm



Model	P/N	Bearing	(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KDE0504PKS2		○	5	0.21	1.0	6000	6.5	0.12	25.5	28
KDE0504PKS3		○	5	0.14	0.7	4500	5.2	0.08	22.8	28
KDE0504PKB2		○	5	0.21	1.0	6500	7.0	0.16	29	28
KDE0504PKB3		○	5	0.14	0.7	5300	6.2	0.12	24	28
KDE1204PKVX	MS	●	12	0.13	1.6	8000	10.0	0.24	27.5	30
KDE1204PKV1	MS	●	12	0.10	1.2	7000	8.5	0.19	25.5	30
KDE1204PKV2	MS	●	12	0.07	0.8	6000	7.3	0.14	20	30
KDE1204PKV3	MS	●	12	0.05	0.6	5000	6.0	0.10	18	30
KDE1204PKS2		○	12	0.07	0.9	6000	6.5	0.12	25.5	28
KDE1204PKS3		○	12	0.05	0.6	4500	5.2	0.08	22.8	28
KDE1204PKB2		○	12	0.07	0.9	6400	6.8	0.15	29	28
KDE1204PKB3		○	12	0.05	0.6	5000	6.0	0.11	24	28
KDE1204PKB1	MS	○	12	0.10	1.2	7200	8.9	0.21	26	30
KDE1204PKB2	MS	○	12	0.07	0.8	6200	7.7	0.16	21.5	30
KDE1204PKB3	MS	○	12	0.05	0.6	5200	6.3	0.11	18.5	30
KDE2404PKS1		○	24	0.07	1.7	7900	8.4	0.16	33.5	35
KDE2404PKS2		○	24	0.05	1.2	6000	6.5	0.12	25.5	20
KDE2404PKS3		○	24	0.03	0.7	4500	5.2	0.08	22.8	20
KDE2404PKB2		○	24	0.04	1.0	6500	7.0	0.16	26.5	20
KDE2404PKB3		○	24	0.03	0.7	5000	6.0	0.11	23.5	20

□

□

4510

:45x45x10mm



Model	P/N	Bearing	(VDC)	(AMP)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
★ KDE1245PFV1	MS	●	12	0.11	1.3	7400	10	0.20	33.5	18
★ KDE1245PFV2	MS	●	12	0.08	1.0	6100	8.3	0.14	29.5	18
KDE1245PFS1-8		○	12	0.07	0.8	6000	8.0	0.14	28.5	20
KDE1245PFS2-8		○	12	0.06	0.7	5200	7.0	0.11	27	20
KDE1245PFS3-8		○	12	0.04	0.5	4000	5.5	0.07	23	20
KDE1245PFB1-8		○	12	0.07	0.8	6300	9.0	0.155	29	20
KDE1245PFB2-8		○	12	0.06	0.7	5500	7.5	0.12	28	20
KDE1245PFB3-8		○	12	0.04	0.5	4500	6.2	0.095	26	20
KDE1245PFB1	OC	○	12	0.12	1.4	7100	9.5	0.16	33.8	20
KDE1245PFB2	OC	○	12	0.08	1.0	5900	8.0	0.13	29	20
KDE1245PFB3	OC	○	12	0.05	0.6	4400	6.1	0.10	23	20
KDE1245PFB1	MS	○	12	0.11	1.3	7500	10.2	0.20	37	18
KDE1245PFB2	MS	○	12	0.08	1.0	6600	8.9	0.15	33.5	18

□