

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1212030002](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Valve Connector, Form B-10mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black, Silicone Gasket



**Documents:**  
[Drawing \(PDF\)](#) [Packaging Specification PK-121203-C92-001 \(PDF\)](#)  
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification STR-1251-001 \(PDF\)](#)

**General**  
Product Family Field Attachable / Accessories  
Series [121203](#)  
Form B - 10mm  
IP Rating IP65, IP67  
Material - Contact Brass  
Overview [mPm DIN Valve Connectors](#)  
Product Name mPm  
Type Field Attachable Connector  
UPC 883906916268

**Physical**  
Cable Diameter N/A  
Coupling Type External Thread  
Diagnostics / LEDs No  
Diagnostics Port No  
Gender N/A  
Keyway None  
Material - Connector Body Polyamide  
Material - Coupling Nut N/A  
Material - Plating Mating Silver  
Net Weight 19.435/g  
Orientation 90° Angle  
Pitch - Mating Interface 10.00mm  
Poles 2  
Temperature Range - Operating -40°C to +125°C  
Wire Size AWG N/A

**Electrical**  
Current - Maximum per Contact 16.0A  
Voltage - Maximum 250V AC/DC

**Material Info**  
Engineering Number C92200N0U

**Reference - Drawing Numbers**  
[Packaging Specification](#) PK-121203-C92-001  
[Product Specification](#) PS-121201-001-001, STR-1251-001  
[Sales Drawing](#) SD-121203-001

**EU ELV**  
**Not Relevant**

**EU RoHS** **China RoHS**  
**Compliant with Exemption 6(c)**  
**REACH SVHC**  
Contained Per - ED/71/2019 (16 July 2019)  
Lead  
**Halogen-Free**  
**Status**  
**Low-Halogen**  
For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | 50 Image     |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Relevant |

**Search Parts in this Series**  
[121203](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION