



# PP2 Series





US RoHS

NEW



## Suggested Panel Cutout



## FEATURES:

- Push-Pull or Momentary Functions
- Various Actuator and Terminal Options
- High Ratings with UL Approvals

## SPECIFICATIONS:

**ELECTRICAL RATING:** 16A 125VAC [cURus]  
12A 250VAC [cURus]  
1hp 125/250VAC [cURus]  
**TEMPERATURE:** 0°C to 85°C [cURus]  
**ELECTRICAL LIFE:** 6,000 Cycles [cURus]  
**CONTACT RESISTANCE:** 50mΩ Max.


## MATERIALS:

**Body:** Polyamide 6/6  
**ACTUATOR:** Polyamide 6/6  
**CONTACTS:** Silver Alloy  
**TERMINALS:** Silver Plated Brass




PP2-4U7-2B2

## Actuator Options




21.7mm Straight



20.8mm Push-Pull

## Terminal Options



6.3mm Tab

4.8mm Tab

PP2-4H7-2A2



| Series | Terminal Type                                        | Function                                                                | Rating                                         | Body Color             | Actuator Height                                                          | Actuator Color |
|--------|------------------------------------------------------|-------------------------------------------------------------------------|------------------------------------------------|------------------------|--------------------------------------------------------------------------|----------------|
| PP2    | 1 - 4.8mm Tabs, Vertical<br>4 - 6.3mm Tabs, Vertical | H - On-(On)<br>U - On <sub>2</sub> -On <sub>1</sub> -(On <sub>2</sub> ) | 7 - 16A 125VAC<br>12A 250VAC<br>1HP 125/250VAC | 1 - Black<br>2 - White | A - 21.7mm Straight*<br>B - 18.3mm Push-Pull**<br>C - 20.8mm Push-Pull** | 2 - White      |

Notes:  
\* = Available with H function only.  
\*\* = Available with U function only.

## EXAMPLE PART NUMBERS:

PP2-4H7-2A2 2P On-(On)  
6.3mm Tab, 19.7mm Straight Actuator  
PP2-4U7-2B2 2P On<sub>2</sub>-On<sub>1</sub>-(On<sub>2</sub>)  
6.3mm Tab, 16.3mm Push-Pull Actuator