

Resonators > CERALOCK (MHz) > Part Number

How to check EU RoHS Compliant of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specification

Global Part Number	CSTCE10M0G55Z-R0
Previous Part Number	
Nominal Frequency	10.000MHz
Initial Tolerance	±0.5%
Temp. Stability	±0.2%
Temperature Range	-40 to +125°C
Wash	Not Available
Ultrasonic Wash	Not Available
Built-in Load Capacitance	33pF
Use	For consumer electronics

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	3000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Details

- ?  [Part Numbering](#)
- ?  [Appearance](#)
- ?  [Dimensions](#)
- ?  [Features, Applications](#)
- ?  [Temperature Characteristics](#)
- ?  [Basic Oscillation Circuit](#)
- ?  [Standard Land Pattern Dimensions](#)
- ?  [Notice \(storage and operating condition\)](#)
- ?  [Notice \(rating\)](#)
- ?  [Notice \(soldering and mounting\)](#)
- ?  [Notice \(handling\)](#)
- ?  [Packaging](#)
- ?  [Minimum Quantity\[Supplementation\]](#)

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first.
Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.