

CIOC 4-20-1,6-F

Order No.: 1701197



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1701197>

Plug component, Nominal current: 3 A, Number of positions: 4, Pitch: 2 mm, Color: blue, Metal surface: Au

Commercial data

GTIN (EAN)	4 046356 030380
sales group	E194
Pack	50 pcs.
Customs tariff	85366990
Catalog page information	Page 175 (NTK-2010)

Product notes

WEEE/RoHS-compliant since:
02/25/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions / positions

Pitch	2 mm
Dimension a	6 mm
Number of positions	4

Technical data

Range of articles	CIOC-F
Connection in acc. with standard	EN-VDE
Nominal current I_N	3 A
Nominal voltage U_N	32 V
Maximum load current	3 A
Insulating material	PBT/PC
Inflammability class acc. to UL 94	V0

Connection data

Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	0.25 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	20

Certificates / Approvals




Certification

CUL, UL

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;