

For use with: TCP 12, 24, 42, 48, 55, TCPS, FE 50 M

Longlife soldering tips are made of pure copper and then iron plated.

With proper care they are always wettable. Special tips and tips with one side wettable on request. Effective temperatures may vary $\pm 3\%$.



Model	Width A		Thickness B		Order-No. with standard temperature range				
	mm	mm			260°C	310°C	370°C	425°C	480°C
Chisel tip	0.8	0,4			PT-H 5	PT-H 6	PT-H 7	PT-H 8	-
	1.6	0,7			5 41 115 99	5 41 116 99	5 41 117 99	5 41 118 99	
					PT-A 5	PT-A 6	PT-A 7	PT-A 8	-
					5 41 125 99	5 41 126 99	5 41 127 99	5 41 128 99	
	2.4	0,8			PT-B 5	PT-B 6	PT-B 7 ①	PT-B 8	PT-B 9
					5 41 135 99	5 41 136 99	5 41 137 99	5 41 138 99	5 41 139 99
	3.2	0,8			PT-C 5	PT-C 6	PT-C 7	PT-C 8	PT-C 9
					5 41 145 99	5 41 146 99	5 41 147 99	5 41 148 99	5 41 149 99
Chisel tip	4.6	0.8			PT-D 5	PT-D 6	PT-D 7	PT-D 8	PT-D 9
					5 41 155 99	5 41 156 99	5 41 157 99	5 41 158 99	5 41 159 99
	5.6	1,2			-	PT-E 6	PT-E 7	PT-E 8	PT-E 9
				-	-	5 41 167 99	5 41 168 99	5 41 169 99	
Long tip	1.2	0,4			PT-K 5	PT-K 6	PT-K 7	PT-K 8	-
					5 41 175 99	5 41 176 99	5 41 177 99	5 41 178 99	
	2.0	1,0			PT-L 5	PT-L 6	PT-L 7	PT-L 8	-
					5 41 185 99	5 41 186 99	5 41 187 99	5 41 188 99	
	3.2	1,2			PT-M 5	PT-M 6	PT-M 7	PT-M 8	PT-M 9
					5 41 195 99	5 41 196 99	5 41 197 99	5 41 198 99	5 41 199 99
Round tip	ø 2.4				-	-	PT-BS 7	PT-BS 8	PT-BS 9
						5 41 207 99	5 41 208 99	5 41 209 99	
	ø 3.2				-	-	PT-CS 7	PT-CS 8	PT-CS 9
					-	-	5 41 217 99	5 41 218 99	5 41 219 99
	ø 5.0			-	-	PT-DS 7	PT-DS 8	PT-DS 9	
						5 41 227 99	5 41 228 99	5 41 229 99	
Round tip, spade	1.2				PT-F 5	PT-F 6	PT-F 7	PT-F 8	PT-F 9
					5 41 235 99	5 41 236 99	5 41 237 99	5 41 238 99	5 41 239 99
	1.6				PT-AA 5	PT-AA 6	PT-AA 7	PT-AA 8	PT-AA 9
					5 41 245 99	5 41 246 99	5 41 247 99	5 41 248 99	5 41 249 99
	2.4				PT-BB 5	PT-BB 6	PT-BB 7	PT-BB 8	PT-BB 9
					5 41 255 99	5 41 256 99	5 41 257 99	5 41 258 99	5 41 259 99
	3.2			-	-	PT-CC 7	PT-CC 8	PT-CC 9	
						5 41 267 99	5 41 268 99	5 41 269 99	
	5.0			-	-	PT-DD 7	PT-DD 8	PT-DD 9	
						5 41 277 99	5 41 278 99	5 41 279 99	
Long tip, conical	0.8				PT-O 5	PT-O 6	PT-O 7	PT-O 8	-
					5 41 285 99	5 41 286 99	5 41 287 99	5 41 288 99	
	0.4				-	-	PT-S 7	PT-S 8	-
						5 41 367 99	5 41 368 99		
Chisel tip	1.6	0,7			PT-R 5	PT-R 6	PT-R 7	PT-R 8	-
					5 41 295 99	5 41 296 99	5 41 297 99	5 41 298 99	
Chisel tip, slightly bent, one side wettable	3.2	1,2			PT-MX 5	PT-MX 6	PT-MX 7	PT-MX 8	-
					5 41 305 99	5 41 306 99	5 41 307 99	5 41 308 99	
							PT-P 7		
							5 41 347 99		

Tool for tip exchange
(part of the cleaning tool)



5 87 060 43