


Dimensions Inches (mm)

Style	Cast Iron									
	1-Gang Deep	2-Gang Deep	3-Gang Deep	1-Gang Shallow	2-Gang Shallow	3-Gang Shallow				
										
Collar Material: Brass Aluminum	B2436* BA2436*	B243641* BA243641*	B4233 BA4233	B423341 BA423341	B4333 BA4333	B433361 BA433361	B2437* –	B2414* BA2414*	B4214 BA4214	B4314 –
Min. Depth of Pour	3.75" (95.3)	3.75" (95.3)	3.75" (95.3)	3.00" (76.2)	2.00" (50.8)	2.00" (50.8)	2.00" (50.8)			
Adjustability	Fully	Fully	Fully	Fully	Semi	Semi	Semi			
Before Pour External Height Adjustment	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)	1.25" (31.8)			
After Pour Internal Height Adjustment	.38" (9.5)	.63" (15.9)	.63" (15.9)	.38" (9.5)	–	–	–			
Cubic Inch (cm3) Capacity Per Gang	33.0 cu. in. (540.7 cm³)	36.5 cu. in. (598.1 cm³)	34.8 cu. in. (570.3 cm³)	30.0 cu. in. (491.7 cm³)	16.0 cu. in. (262.2 cm³)	16.0 cu. in. (262.2 cm³)	16.0 cu. in. (262.2 cm³)			
Dimensions – A	3.20" (81.3)	3.38" (85.9)	3.38" (85.9)	2.90" (73.7)	2.00" (50.8)	2.00" (50.8)	2.00" (50.8)			
Dimensions – B	4.69" (119.1)	4.84" (122.9)	4.90" (122.5)	4.69" (119.1)	5.46" (138.7)	5.46" (138.7)	5.46" (138.7)			
Dimensions – C	4.69" (119.1)	8.06" (204.7)	11.41" (289.8)	4.69" (119.1)	4.19" (106.4)	7.49" (190.2)	10.7" (271.8)			
Dimensions – D	4.36" (110.7)	4.36" (110.7)	4.36" (110.7)	4.36" (110.8)	4.38" (111.3)	4.38" (111.3)	4.38" (111.3)			
Dimensions – E	3.19" (81.0)	6.42" (163.1)	9.64" (244.9)	3.20" (81.3)	3.19" (81.0)	6.38" (162.1)	9.56" (242.8)			
Threaded Access Holes	(4) ¾" (4) 1"	(6) ¾" (4) 1" & (2) ¾"	(8) ¾" (6) 1" & (2) ¾"	(4) ¾"	(2) ¾"	(4) ¾"	(6) ¾"			
Concrete Cover Included	✓	✓	✓	✓	✓	✓	✓			
Closure Plugs Included	✓	✓	✓	✓	✓	✓	✓			
Removable LV Barrier	–	✓	✓	–	–	–	–			

Note: UL File Number E92074.
CSA File Number LR18416.
*Suitable for single service applications only.

Carpet Flanges

Tapered Flange

Number of Gangs	1-Gang	2-Gang	3-Gang
Dimensions	6.00" x 4.85"	6.00" x 8.13"	6.00" x 11.34"
Brass	SB3083	SB3084	SB3085
Aluminum	SA3083	SA3084	SA3085
Clear Polycarbonate	S3083	S3084	S3085



Covers – One Required per Gang

Brass	S3825	S3625	S3826	S2425	S2625	S2825	S3813
Aluminum	SA3825	SA3625	SA3826	SA2425	SA2625	–	SA3813
Dimensions	4.15" x 2.99"	4.15" x 2.99"	4.15" x 2.99"	4.15" x 2.99"	4.15" x 2.99"	4.15" x 2.99"	4.15" x 2.99"
							
	Duplex Flap	Duplex Screw	Style Line® Decorator Opening	2 1/8" x 3/4" Combination	2 1/8" x 1" Combination	2 1/8" Single Receptacle	Blank

Dimensions in Inches (mm)