

## 3640ITP125P63 Flat

EAN 4031582337358


Swivel castor, housing made of heavy pressed steel, bright zinc plated, blue passivated, precision ball bearing swivel head, sealed, wheel axle with nut, plate fitting.

Wheel centre made of Aluminium, Tread: Polyurethane, casted, precision ball bearing

### Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 125 mm         |
| Width of Tread         | 50 mm          |
| Size of Plate          | 137 x 105 mm   |
| Plate hole centres     | 105 x 80/75 mm |
| Plate hole             | 11 mm          |
| Offset                 | 55 mm          |
| Swivel Interference    | 235 mm         |
| Overall height         | 178 mm         |
| Temperature            | - 20 / + 60 °C |
| Standard               | EN 12532       |
| Weight                 | 2.941 kg       |
| Swivel Radius          | 117.5 mm       |
| Hardness of tread      | A 92 Shore     |
| Load capacity          | 500 kg         |
| Load capacity (static) | 1000 kg        |

|                      |   |   |   |   |   |
|----------------------|---|---|---|---|---|
| Roll performance     | + | + | + | + | + |
| Movement noise       | + | + | + | + | + |
| Attrition            | + | + | + | + | + |
| Corrosion resistance | + | + | + | + | + |



## 3640ITP125P63 Flat

EAN 4031582337358

