

tightening torque/thread 1.0 Nm/M 3 Inspection Test Pattern Size A 4

Type	Cat.-No.		Qty.p.pck.
SR 4 DRL	41211.2	beige	100
SR 4 DRL	41211.5	blue	100


Ratings:

	UL	CSA	DIN-VDE	IEC
Rated Voltage	600 V	600 V	611	947-7-1
Rated Current	20 A AWG 12	26 A	500 V	500 V
			26 A	24 A

Max Rated Cross Section

Single Wire (solid)	0.2-4 mm ²
Stranded Wire (flexible)	0.2-2.4 mm ²
Wire Size	AWG 22-12

Dimensions	TS 32	TS 35
LxHxW (mm)	67x6x52	67x6x47
Stripped Length	9 mm	



tightening torque/thread 2.0 Nm/M 4 Inspection Test Pattern Size A 5

Type	Cat.-No.		Qty.p.pck.
SR 10	41005.2	beige	100
SR 10	41005.5	blue	100

Additional colors available. See page 114.

Ratings:

	UL	CSA	DIN-VDE	IEC
Rated Voltage	600 V	600 V	611	947-7-1
Rated Current	65 A AWG 8	55 A	750 V	800 V
			61 A	57 A

Max Rated Cross Section

Single Wire (solid)	0.2-10 mm ²
Stranded Wire (flexible)	0.2-10 mm ²
Wire Size	AWG 22-8

Dimensions	TS 32	TS 35
LxHxW (mm)	48x8x52	48x8x47
Stripped Length	12 mm	

Type:	Cat.-No.	Qty.p.pck.	Terminal accessories	Type:	Cat.-No.	Qty.p.pck.
AP 2.5 RL	2575.2 beige 2575.5 blue	50	End plate	AP 2.5-10	2001.2 beige 2001.5 blue	50
			Isolation partition	TW 2.5-10	2002.2 beige 2002.5 blue	50
TRS 1	2003.2 beige	100	Separator	TRS 1	2003.2 beige	100
ES 32/35 Combi	1424.2 beige		End bracket	ES 32/35 Combi	1424.2 beige	
ES 32/K/ST	2827.0	50		ES 32/K/ST	2827.0	50
ES 35/2/K	2826.2 beige		End bracket	ES 35/2/K	2826.2 beige	
ES 35/K/ST	2828.0	50		ES 35/K/ST	2828.0	50
STB 14/2.3	2006.0	50	Test socket	STB 14/4	2050.0	50
PS 2.3	2007.0	20	Test plug	PS 4	2051.0	20
QL 2	2008.0	50	Switchable link	QL 2	2053.0	50
VH 19	2009.0	100	Connection sleeve	VH 19	2009.0	100
BS M 3x25	2010.0	100	Screw	BS M 3x25	2010.0	100
AD 4	2011.0	50	Warning tag (German)	AD 4	2054.0	50
AD 4 E	2494.0	50	Warning tag (English)	AD 4 E	2495.0	50
BSK M 3x22	2012.0	100	Plastic screw for warning tag	BSK M 3x22	2012.0	100
Q2/Q1 2	2019.0/2740.2	50	Cross-connection/Insulated cross-connection	Q2/Q1 2	2060.0/2750.2	50
Q3/Q1 3	2020.0/2741.2	50	Cross-connection/Insulated cross-connection	Q3/Q1 3	2061.0/2751.2	50
Q4/Q1 4	2021.0/2742.2	20	Cross-connection/Insulated cross-connection	Q4/Q1 4	2062.0/2752.2	20
Q10/Q1 10	2022.0/2743.2	10	Cross-connection/Insulated cross-connection	Q10/Q1 10	2063.0/2753.2	10