





REV.	DATE	DESCRIPTION
A	01/10/04	INITIAL RELEASE
B	05/25/06	ADD CABLE LISTING TO DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .324"
 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex				
7						DRAWN	G.R.S.	05/25/06						
6						CHECKED				PART DESCRIPTION BNC CRIMP PLUG CABLE (FOR BELDEN 8281 CABLE)				
5						ISSUED								
4	FERRULE	COPPER	NICKEL	1		SHEET		1 OF 1		PART NO. 112509				
3	CONTACT PIN	BRASS	GOLD	1										
2	INSULATOR	DELTRIN	NATURAL	1					DWG. NO. 112509.DWG					
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE C:/112/112509.DWG		REV.	B	SIZE	A	SCALE	NA