





www.fciconnect.com			surface ☒ tolerance std ISO 1302 ISO 406 ISO 1101			projection 		 mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	M PESSON	2005-10-11	ANGULAR	0.X	±0.3	size A2	ECN	Scale 2:1	LS07-0273
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	±0.1				
Chr			0° ±2°	0.XXX	±0.05				
Appr			Product family			- Spec ref			
			SUB FEMALE DW EUROPE foot print			C01-8639-2316		Rev. C	
			full power right angle press fit			CUSTOMER		sheet 2 of 5	
			catalog no						

SCALE: 4



PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS8IC5A40LF	40	200	without	without
D*LxWxS8IC5A40LF	40	200	insert M3	without
D*OxWxS8IC5A40LF	40	200	insert UNC 4.40	without
D*VxWxS8IC5A40LF	40	200	female screw UNC 4.40	without
D*xWxS8IC5M40LF	40	200	without	metal bracket
D*LxWxS8IC5M40LF	40	200	insert M3	metal bracket
D*OxWxS8IC5M40LF	40	200	insert UNC 4.40	metal bracket
D*VxWxS8IC5M40LF	40	200	female screw UNC 4.40	metal bracket

shell size

E
A
A
B
C

LAYOUTS
xWx
2V2
3V3
3W3
5W5
8W8

PART NUMBER	AMPS	MATINGS/ UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*xWxS8IC6A40LF	40	500	without	without
D*LxWxS8IC6A40LF	40	500	insert M3	without
D*OxWxS8IC6A40LF	40	500	insert UNC 4.40	without
D*VxWxS8IC6A40LF	40	500	female screw UNC 4.40	without
D*xWxS8IC6M40LF	40	500	without	metal bracket
D*LxWxS8IC6M40LF	40	500	insert M3	metal bracket
D*OxWxS8IC6M40LF	40	500	insert UNC 4.40	metal bracket
D*VxWxS8IC6M40LF	40	500	female screw UNC 4.40	metal bracket

www.fciconnect.com		surface ISO 1302	-	tolerance std ISO 406 ISO 1101	projection mm	size A2		Scale 2:1	
Dr M PESSON 2005-10-11		TOLERANCES UNLESS OTHERWISE SPECIFIED		0.X ±0.3	size A2	ECN LS07-0273		Spec ref	
Eng P LEGARE 2005-10-11		ANGULAR	LINEAR	0.XX ±0.1					
Chr		0° ±2°		0.XXX ±0.05					
Appr		Product family		-					
FCi		SUB FEMALE DW EUROPE foot print		deg no		C01-8639-2316		Rev. C	
full power right angle press fit		catalog no		-		CUSTOMER		sheet 3 of 5	

