




Model 2



Window Diameter 1.0", 1.05", 1.13"





2SFT






2SHT



2RL



2DRL



Application:

Generally for ammeter use only.

Frequency:

50-400Hz

Insulation Level:

600 Volts, 10kV BIL full wave

Rating Factor:

2.0 @ 30°C amb

- Flexible leads are UL 1015 105°C, CSA approved #16 AWG, 24" long
- Non-standard length to be specified
- Terminals are brass studs No. 8-32 UNC with one flat washer, lockwasher and regular nut
- SHT and SFT case styles also available as SHL and SFL with leads
- Mounting bracket kit when required for Model 2SHT
- Approximate weight: 0.5 lb

Approvals



UL 257877

CSA 223647

Catalogue Number	Current Ratio	Models 2SFT, 2SHT, 2RL		Model 2DRL	
		Accuracy at 60Hz	Burden VA at 60Hz	Accuracy at 60Hz	Burden at 60Hz
2**-500	50:5	± 3%	2.0	± 2%	1.5
2**-600	60:5	± 2%	2.0	± 1%	2.5
2**-750	75:5	± 2%	2.0	± 1%	3.5
2**-800	80:5	± 2%	2.0	± 1%	4.0
2**-101	100:5	± 1%	2.0	± 1%	5.0
2**-121	120:5	± 1%	2.5	± 1%	5.0
2**-1250	125:5	± 1%	2.5	± 1%	5.0
2**-151	150:5	± 1%	4.0	± 1%	8.0
2**-201	200:5	± 1%	4.0	± 1%	10.0
2**-251	250:5	± 1%	6.0	± 1%	12.5
2**-301	300:5	± 1%	8.0	± 1%	15.0
2**-401	400:5	± 1%	10.0	± 1%	20.0

***NOTE:** When ordering, prefix Catalogue Number with model designation required, i.e. 2SFT-301, 2RL-301 or 2DRL-301, etc.