


Model 1948-C Cable Assembly – BNC Male Connector To TNC Male Connector



MATERIALS:

Connector: 1st End – BNC Male

Body & Fittings: Brass, Tarnish Resisting Plating

Center Contact: Gold Plated Brass per MIL-C-39012

Finish: Tarnish Resistant

Cable: RG58C/U, .195" O.D. Color: Black

Cap. Pf/ft.: 30.8

Connector: 2nd End – TNC Male

Body & Fittings: Brass, Tarnish Resistant Plating

Center Contact: Gold Plated Brass per MIL-C-39012

RATINGS:

Operating Temperature: +80°V. (+176°F.) Max.

Operating Voltage: 500 VRMS Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 1948-C-XX

XX = Length in inches. Std. Lengths: 12", 24", 36", 48", 60"

Additional lengths can be quoted upon request

Ordering Example: 1948-C-36, Cable length will be 36" long

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1948-C-12](#) [1948-C-24](#) [1948-C-60](#) [1948-C-36](#) [1948-C-48](#)