

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFLCCX8-10A-L
 - PDFLCCX8-14A-L
 - Part Drawings
 - PDFCopper, Long..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click to remove) Search Tips

Part Description > Flex lug, long barrel, #6 AWG, 2 hole, 1/4" stud holes, .63 hole spacing.

Your search criteria matched only one product, shown below



- For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors
- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull-out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCCX614A-L
RoHS Compliancy Status	Compliant
Part Description	Flex lug, long barrel, #6 AWG, 2hole, 1/4" stud holes, .63 hole spacing.
Material	Tin-Plated Copper
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.49
Length (mm)	63.3
Class G,H, I, K, M	#6 AWG
Diesel Locomotive	#6 AWG
Stud Hole Size (In.)	1/4
Stud Hole Spacing (In.)	0.63
Tongue Width (In.)	0.48
Barrel Length (In.)	1.07
Angle	Straight
Barrel Length (mm)	27.2
CE Compliant	No
Figure No.	1
Panduit Color Code	Blue
PANDUIT Die Color & Die No.	Blue P24
Panduit Die Index No.	P24
Pattern	B
Pricing Description	Copper Comp. Lug, 2 Hole, #6 AWG Flex, 1/4" (6.4mm) Stud, .63" (16mm) Hole Spacing
Stud Hole Size (mm)	6.4
Tongue Thickness	0.08
Tongue Type	Standard
Tongue Width (mm)	12.2
Tool	CT-1700, CT-930, CT-2930/L, CT-2930/LE
Wire Strip Length (In.)	1 1/8
Wire Strip Length (mm)	29.0
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	7
T&B Die Index No.	24
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.