





ROHS



RECOMMEND P.C.B. LAYOUT
HOLE LAYOUT



How to order Please replace "X" with appropriate coding listed in the table below.
Part Number

7110 - XXS - XX - X - D - X

No. of Connectors
06,08,10,12,14,16,20,
24,26,30,34,40,44,50,
60,64 Connectors

Connector Type
Definition Code
Straight S
Right Angle R

Contact Plating
Definition Code
Gold Flash GF
Gold & Tin GT
Tin Flash TF
3µ 03
5µ 05
10µ 10
15µ 15
30µ 30

Color
Definition Code
Black B
White W
Blue U
Yellow Y
Green G

Pin Length
Definition Code
D 031
If you desire an
other length, by
marking put
desired length in
the D.

No. of Gaps
Definition Code
1 Gap 1
3 Gaps 3

MATERIALS :

1. HOUSING : P.B.T. (UL 94V-0), BLACK.
2. TERMINAL : S.Q. 0.64mm BRASS, GOLD PLATING.

SPECIFICATION

1. CURRENT RATING : 3 AMP. MAX.
2. DIELECTRIC WITHSTAND VOLTAGE :
1,000V AC R.M.S. FOR 1 MINUTE.
3. INSULATION RESISTANCE : 5,000M OHMS MIN.
AT 1,000V DC.
4. OPERATING TEMPERATURE : -55°C TO +105°C.

Number Of Position	DIMENSIONS		
	A	B	C
06	15.24[0.600]	12.94[0.509]	5.08[0.200]
08	17.78[0.700]	15.48[0.609]	7.62[0.300]
10	20.32[0.800]	18.02[0.709]	10.16[0.400]
12	22.86[0.900]	20.56[0.809]	12.70[0.500]
14	25.40[1.000]	23.10[0.909]	15.24[0.600]
16	27.94[1.100]	25.64[1.009]	17.78[0.700]
20	33.02[1.300]	30.72[1.209]	22.86[0.900]
24	38.10[1.500]	35.80[1.409]	27.94[1.100]
26	40.64[1.600]	38.34[1.509]	30.48[1.200]
30	45.72[1.800]	43.42[1.709]	35.56[1.400]
34	50.80[2.000]	48.50[1.909]	40.64[1.600]
40	58.42[2.300]	56.12[2.209]	48.28[1.900]
44	63.50[2.500]	61.20[2.409]	53.34[2.100]
50	71.12[2.800]	68.82[2.709]	60.96[2.400]
60	83.82[3.300]	81.52[3.209]	73.66[2.900]
64	88.90[3.500]	86.60[3.409]	78.74[3.100]

- *Less than 44 Pins only 1 gap type.
*50 Pins have 1 gap or 3 gaps type.
*60,64 Pins only 3 gaps type.

TOP WILLING CO., LTD.

SCALE				DRAW NO.	
NONE				D001	
SIZE	SHEET	REV.	DATE		
A4	1 OF 1	A	2003.08.15		