




	I	2	3	4	5	6	7	8																																																																																								
A	REFERENCE SPECIFICATIONS -NFC 93425 (in compliance with HE 507) PHYSICAL CHARACTERISTICS -INSULATOR MATERIAL: THERMOPLASTIC UL94V0 -CONTACT MATERIAL: PHOSPHOR BRONZE(SIGNAL CONTACT) GOLD OVER NICKEL -ACCESSORIES: STEEL FOR BRACKETS Cadmium plated, yellow passivation B -SHELLS: STEEL Cadmium plated, yellow passivation ELECTRICAL CHARACTERISTICS -NOMINAL CURRENT: 7.5A (SIGNAL CONTACT) -CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL) -CONTACT/CONTACT : >=1000 V C ENVIRONMENTAL CHARACTERISTICS -CONTACT/GROUND : >=1200 V -INSULATION RESISTANCE: >=5000 MOhms D - CLIMATIC CATEGORY: 55/125/21 TEMPERATURE RANGE -55°C TO +125°C DAMP HEAT STEADY STATE 56 DAYS SALT SPRAY 48 HOURS E F			Series Shell size: E A B C D (see sheet 3) M :Characteristics for the DM serie Front accessory definition (see sheet 2) blank :without accessory L :threaded insert M3 O :threaded insert UNC 4-40 V :female screw UNC 4-40 Layout of contacts (see sheet 3) Contacts S :Socket Termination type 5 Right angle/Europe standard Plating 00 Right angle 500 matings/unmatings 43 Right angle 500 matings/unmatings for harsh environment PCB accessories definition(see sheet 2) blank :Plastic brackets C :Without brackets M :Metal brackets N :Obligatory indication for HE 507					DBML13W3S500MN			13W3 FOR EXAMPLE 																																																																																				
FCI Copyright FCI.				<table><tr><td>rev</td><td>ecn no</td><td>dr</td><td>date</td></tr><tr><td>A</td><td>LS06-0174</td><td>MPE</td><td>2006/11/14</td></tr><tr><td>-</td><td>-</td><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td><td>-</td><td>-</td></tr><tr><td>-</td><td>-</td><td>-</td><td>-</td></tr></table> <table><tr><td colspan="3">www.fciconnect.com</td><td>surface - ISO 1302</td><td>tolerance std ISO 406 ISO 1101</td><td>projection TOLERANCES UNLESS OTHERWISE SPECIFIED</td><td>size A2</td><td>mm Scale 2:1</td></tr><tr><td>Dr</td><td>M.PESSON</td><td>2006/11/14</td><td>ANGULAR</td><td>0.X</td><td>±0.3</td><td rowspan="3">ECN LS06-0174</td><td rowspan="3">Rev. A</td></tr><tr><td>Eng</td><td>M.PESSON</td><td>2006/11/14</td><td rowspan="2">LINEAR</td><td>0.XX</td><td>±0.1</td></tr><tr><td>Chr</td><td>P.LEGARE</td><td>2006/11/14</td><td>0° ±2°</td><td>0.XXX</td><td>±0.05</td></tr><tr><td>Appr</td><td>P.LEGARE</td><td>2006/11/14</td><td colspan="3">Product family</td><td>-</td><td>Spec ref</td></tr><tr><td colspan="3">FCI</td><td colspan="2">title SUB FEMALE DMW EUROPE foot print</td><td colspan="2">dwg no C01-8637-1749</td><td></td></tr><tr><td colspan="3"></td><td colspan="2">mixed power right angled solder</td><td colspan="2"></td><td></td></tr><tr><td colspan="3"></td><td colspan="2">catalog no</td><td colspan="2">-</td><td></td></tr></table>					rev	ecn no	dr	date	A	LS06-0174	MPE	2006/11/14	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	www.fciconnect.com			surface - ISO 1302	tolerance std ISO 406 ISO 1101	projection TOLERANCES UNLESS OTHERWISE SPECIFIED	size A2	mm Scale 2:1	Dr	M.PESSON	2006/11/14	ANGULAR	0.X	±0.3	ECN LS06-0174	Rev. A	Eng	M.PESSON	2006/11/14	LINEAR	0.XX	±0.1	Chr	P.LEGARE	2006/11/14	0° ±2°	0.XXX	±0.05	Appr	P.LEGARE	2006/11/14	Product family			-	Spec ref	FCI			title SUB FEMALE DMW EUROPE foot print		dwg no C01-8637-1749						mixed power right angled solder								catalog no		-		
rev	ecn no	dr	date																																																																																													
A	LS06-0174	MPE	2006/11/14																																																																																													
-	-	-	-																																																																																													
-	-	-	-																																																																																													
-	-	-	-																																																																																													
-	-	-	-																																																																																													
-	-	-	-																																																																																													
www.fciconnect.com			surface - ISO 1302	tolerance std ISO 406 ISO 1101	projection TOLERANCES UNLESS OTHERWISE SPECIFIED	size A2	mm Scale 2:1																																																																																									
Dr	M.PESSON	2006/11/14	ANGULAR	0.X	±0.3	ECN LS06-0174	Rev. A																																																																																									
Eng	M.PESSON	2006/11/14	LINEAR	0.XX	±0.1																																																																																											
Chr	P.LEGARE	2006/11/14		0° ±2°	0.XXX			±0.05																																																																																								
Appr	P.LEGARE	2006/11/14	Product family			-	Spec ref																																																																																									
FCI			title SUB FEMALE DMW EUROPE foot print		dwg no C01-8637-1749																																																																																											
			mixed power right angled solder																																																																																													
			catalog no		-																																																																																											
REV F - 2006-04-17				PDS: Rev :A STATUS: Released Printed: Jun 18, 2015 Printed: Jun 17, 2015																																																																																												



FRONT ACCESSORY	Blank Without	L O insert M3 insert UNC 4.40	V Female screw UNC 4.40	Blank Without	L O insert M3 insert UNC 4.40	V Female screw UNC 4.40
PCB ACCESSORIES	C Without bracket	C Without bracket	C Without bracket	M Metal bracket	M Metal bracket	M Metal bracket




FRONT ACCESSORY	Blank Without	L O insert M3 insert UNC 4.40	V Female screw UNC 4.40
PCB ACCESSORIES	Blank Plastic bracket	Blank Plastic bracket	Blank Plastic bracket


Printed: Jun 18, 2015

PART NUMBER	MATINGS / UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*MxWxS500CN	500	without	without
D*MLxWxS500CN	500	insert M3	without
D*MOxWxS500CN	500	insert UNC 4.40	without
D*MVxWxS500CN	500	female screw UNC 4.40	without
D*MxWxS500MN	500	without	metal bracket
D*MLxWxS500MN	500	insert M3	metal bracket
D*MOxWxS500MN	500	insert UNC 4.40	metal bracket
D*MVxWxS500MN	500	female screw UNC 4.40	metal bracket
D*MxWxS500N	500	without	plastic bracket
D*MLxWxS500N	500	insert M3	plastic bracket
D*MOxWxS500N	500	insert UNC 4.40	plastic bracket
D*MVxWxS500N	500	female screw UNC 4.40	plastic bracket

PART NUMBER	MATINGS / UNMATINGS	FRONT ACCESSORY	PCB ACCESSORIES
D*MxWxS543CN	500	without	without
D*MLxWxS543CN	500	insert M3	without
D*MOxWxS543CN	500	insert UNC 4.40	without
D*MVxWxS543CN	500	female screw UNC 4.40	without
D*MxWxS543MN	500	without	metal bracket
D*MLxWxS543MN	500	insert M3	metal bracket
D*MOxWxS543MN	500	insert UNC 4.40	metal bracket
D*MVxWxS543MN	500	female screw UNC 4.40	metal bracket
D*MxWxS543N	500	without	plastic bracket
D*MLxWxS543N	500	insert M3	plastic bracket
D*MOxWxS543N	500	insert UNC 4.40	plastic bracket
D*MVxWxS543N	500	female screw UNC 4.40	plastic bracket


shell size	LAYOUTS
5W1	
11W1	
7W2	
21W1	
17W2	
13W3	
9W4	
25W3	
21WA4	
27W2	
47W1	
24W7	
36W4	

www.fciconnect.com			surface - ☒ ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M.PESSON	2006/11/14	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	M.PESSON	2006/11/14			0.XX	±0.1				
Chr	P.LEGARE	2006/11/14			0.XXX	±0.05				
Appr	P.LEGARE	2006/11/14	Product family					-	Spec ref	
			title SUB FEMALE DMW EUROPE foot print				dwg no C01-8637-1749		Rev. A	
			mixed power right angled solder							
			catalog no -				CUSTOMER		sheet 3 of 9	




Copyright FCi

REV F - 2006-04-17




Copyright FCi.

www.fciconnect.com			surface - ☒ ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	M. PESSON	2006/11/14	ANGULAR	LINEAR	0.X		±0.3		size A2	Scale 2:1	
Eng	M. PESSON	2006/11/14			0.XX		±0.1				
Chr	P. LEGARE	2006/11/14			0.XXX		±0.05				
Appr	P. LEGARE	2006/11/14	0° ±2°				ECN		LS06-0174		
			Product family					-		Spec ref	
			title SUB FEMALE DMW EUROPE foot print					dwg no C01-8637-1749		Rev. A	
			mixed power right angled solder								
catalog no			-					CUSTOMER		sheet 6 of 9	




LAYOUT AND CONNECTOR DIMENSIONS


21WA4



LAYOUT AND CONNECTOR DIMENSIONS





25W3



www.fciconnect.com			surface - 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M. PESSON	2006/11/14	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	M. PESSON	2006/11/14			0.XX	±0.1				
Chr	P. LEGARE	2006/11/14	0° ±2°		0.XXX	±0.05	ECN LS06-0174			
Appr	P. LEGARE	2006/11/14			Product family			-	Spec ref	
			title SUB FEMALE DMW EUROPE foot print mixed power right angled solder			dwg no C01-8637-1749			Rev. A	
			catalog no			CUSTOMER			sheet 7 of 9	








LAYOUT AND CONNECTOR DIMENSIONS



24W7


LAYOUT AND CONNECTOR DIMENSIONS





www.fciconnect.com			surface - ☒ ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M. PESSON	2006/11/14	ANGULAR	LINEAR	0.X		±0.3		size A2	Scale 2:1
Eng	M. PESSON	2006/11/14			0.XX		±0.1			
Chr	P. LEGARE	2006/11/14			0° ±2°		0.XXX		±0.05	
Appr	P. LEGARE	2006/11/14	Product family						- ECN LS06-0174	
									Spec ref	
			SUB FEMALE DMW EUROPE foot print			C01-8637-1749			Rev. A	
			mixed power right angled solder							
catalog no			-			CUSTOMER			sheet 8 of 9	

36W4

LAYOUT AND CONNECTOR DIMENSIONS



SIDE VIEW FOR ALL LAYOUTS



www.fciconnect.com			surface - ☒ ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M.PESSON	2006/11/14	ANGULAR	0.X ± 0.3	size A2	Scale 2:1
Eng	M.PESSON	2006/11/14	LINEAR	0.XX ± 0.1		
Chr	P.LEGARE	2006/11/14	0° $\pm 2^\circ$	0.XXX ± 0.05	ECN LS06-0174	
Appr	P.LEGARE	2006/11/14	Product family		- Spec ref	
			SUB FEMALE DMW EUROPE foot print			Rev. A
			mixed power right angled solder			
catalog no			-			
			CUSTOMER			sheet 9 of 9