

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet  
- PDF-FOPRZ06Y Pro  
- Part Drawings  
- PDF-Fiber Optic ..

How to Buy

- Bill of Material  
- Favorite Products List  
- Locate Distributor


[Home](#) > [Product On-Line Catalog](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

**Text Search: 'FOPPZ24Y'**

Your search criteria matched only one product, shown below

**FOPPZ24Y**



- Used in intrabuilding backbone, building backbone, and horizontal installations for riser (OFCR), plenum (OFCP), and harsh environments
- Interlocking aluminum armor eliminates the need for inner duct or conduit to provide a smaller crush resistant pathway for design flexibility and a lower installed cost
- Available in 6, 12, 24, 36, 48, 72, 96, and 144-fiber counts
- Multimode (OM4, OM3, OM2, and OM1) and singlemode (OS1/OS2) fiber available (optimized fiber available)
- Sheath markings provide positive identification, quality traceability, and length verification
- 900µm standards-based color-coded buffer coating protects fibers during handling and allows for easy identification and stripping
- Cable design and flexible buffer tubes allow for quick breakout and ease of routing
- Opti-Core® 10Gig™ Fiber Optic Cable is designed to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters for OM3 and up to 550 meters for OM4 with an 850nm source per IEEE 802.3ae 10 GbE standard; backward compatible for use with all 50/125µm system requirements

These products are available for sale in the Americas regions only. Contact Customer Service for minimum order quantities, availability, and additional product configurations. Options include fiber counts, jacket colors, hybrid constructions (multiple fiber types within a single cable), flame ratings, subunit counts, indoor/outdoor designs, premium optical performance grades and ribbonized constructions.

Part Number	FOPPZ24Y
RoHS Compliance Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	24-fiber 10Gig™ 50/125µm (OM4) multimode plenum rated indoor interlocking armored cable.
Color	Aqua
Fiber Compatibility	10 GbE 50/125µm
Fiber Cable Type	Interlocking Armored Cable
Fiber Type	Multimode
Fiber Count	24
Flammability Rating	Plenum (OFNP)
Pricing Description	24-Fiber Plenum 50µm 10Gig OM4 Interlocking Armored Cable
Min. Order UOM	FT
Min. Order Qty.	3280
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.