

# WELDED CHAINS AND ACCESSORIES

## CHAINS

Our Welded Steel chains are made to UK and international standards, with the links side welded for extra strength and quality tested. These chains are suitable for all general purpose, engineering, industrial, agricultural and marine applications in conjunction with our range of mild steel accessories.


All products are available as stock items across a wide range of sizes and protective finishes such as zinc, black and hot dip galvanised.

Welded chain assemblies designed to customer specifications are also an important part of this range. Please see our "Assemblies" section for more details on our specialist service.



Ø 1.6 - 12mm

**Welded Straight Link  
(to UK specification)**



Ø 2 - 12mm

**Welded Long Link  
(to DIN 5685 A&C)**



Ø 5 - 16mm

**Welded, Tested and  
Certified Short Link  
Chain (to DIN 766)**



Ø 2.5 - 6mm

**Welded Twisted  
Link Chain**








Ø 6mm

**Spiked Fencing  
Chain**

## ACCESSORIES

|                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |  |  |  |  |  |  |
| <b>Ess Hooks</b>                                                                    | <b>Mending Links</b>                                                                | <b>Quick Links</b>                                                                  | <b>Repair Links</b>                                                                 | <b>Carbine Hooks</b>                                                                | <b>Springhooks to Crue</b>                                                          | <b>Springhooks to Swivel</b>                                                          | <b>Swivel Snap Hooks</b>                                                              | <b>Simplex Hooks</b>                                                                  |

|                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                      |                                                                                       |                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |  |  |  |  |  |  |
| <b>Swivels</b>                                                                      | <b>Ring on Plate</b>                                                                | <b>Welded Rings</b>                                                                 | <b>Eyebolts DIN 580</b>                                                             | <b>Eyenuts DIN 582</b>                                                              | <b>Dee Shackles</b>                                                                  | <b>Bow Shackles</b>                                                                   | <b>Spring Pins</b>                                                                    | <b>Lynch Pins</b>                                                                     |

|                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                       |                                                                                       |                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|  |  |  |  |  |  |  |  |
| <b>Straining Screws</b>                                                             | <b>Woodpost Fittings</b>                                                            | <b>Post Fittings</b>                                                                | <b>Eyebolts</b>                                                                     | <b>Swing Hooks</b>                                                                  | <b>Ringbolts</b>                                                                      | <b>Wire Rope Thimbles and Grips</b>                                                   | <b>Wire Rope</b>                                                                      |

## Mild Steel Straight Link Chains

### U.K. SPECIFICATIONS

welded, test loaded, uncertified



| Product Code | Size     | Wire Ø (mm) | Inside Link Length x Width (mm) | Weight per mtr (kg) | *Maximum Load (kg) |
|--------------|----------|-------------|---------------------------------|---------------------|--------------------|
| 453 02       | 1.6 x 13 | 1.6         | 13 x 4                          | 0.05                | 15                 |
| 453 10       | 2 x 14   | 2.0         | 14 x 5                          | 0.08                | 30                 |
| 193 14       | 2.5 x 14 | 2.5         | 14 x 6                          | 0.11                | 50                 |
| 193 18       | 2.5 x 19 | 2.5         | 19 x 7                          | 0.10                | 50                 |
| 193 22       | 3 x 16   | 3.0         | 16 x 8                          | 0.17                | 85                 |
| 193 24       | 3 x 21   | 3.0         | 21 x 8                          | 0.16                | 80                 |
| 193 28       | 3 x 26   | 3.0         | 26 x 8                          | 0.15                | 80                 |
| 193 32       | 4 x 19   | 4.0         | 19 x 9                          | 0.30                | 130                |
| 193 34       | 4 x 26   | 4.0         | 26 x 9                          | 0.28                | 120                |
| 193 42       | 5 x 21   | 5.0         | 21 x 11                         | 0.50                | 170                |
| 193 44       | 5 x 28   | 5.0         | 28 x 11                         | 0.47                | 160                |
| 193 52       | 6 x 24   | 6.0         | 24 x 12                         | 0.68                | 265                |
| 193 54       | 6 x 33   | 6.0         | 33 x 13                         | 0.62                | 250                |
| 193 60       | 6.5 x 36 | 6.5         | 36 x 14                         | 0.79                | 290                |
| 193 66       | 7 x 38   | 7.0         | 38 x 15                         | 0.91                | 370                |
| 193 75       | 8 x 42   | 8.0         | 42 x 17                         | 1.17                | 460                |
| 193 81       | 10 x 53  | 10.0        | 53 x 18                         | 1.84                | 655                |
| 453 85       | 12 x 61  | 12.0        | 61 x 23                         | 2.59                | 1025               |

**Finishes:** polished; black; bright zinc; hot galvanised

**Supplied:** bulk in hanks; 10m boxes; 10m bags; on reels

\*Maximum load figures quoted are for guidance only. These chains are test loaded, but not certified and should never be used for any overhead lifting, load binding or towing applications.

### TWISTED LINK CHAINS - MILD STEEL

welded, untested



| Product Code | Size     | Wire Ø (mm) | Inside Link Length x Width (mm) | Weight per mtr (kg) | *Maximum Load (kg) |
|--------------|----------|-------------|---------------------------------|---------------------|--------------------|
| 463 25       | 2.5 x 9  | 2.5         | 9 x 4                           | 0.14                | 40                 |
| 463 34       | 3 x 16   | 3.0         | 16 x 5                          | 0.17                | 60                 |
| 463 44       | 4 x 19   | 4.0         | 19 x 5                          | 0.31                | 100                |
| 463 52       | 5 x 21   | 5.0         | 21 x 7                          | 0.53                | 140                |
| 463 62       | 6 x 33   | 6.0         | 33 x 9                          | 0.66                | 150                |
| 463 65       | 6.5 x 36 | 6.5         | 6.5 x 36                        | 0.81                | 160                |

**Finishes:** polished, bright zinc

**Supplied:** bulk in hanks; on reels

\*Maximum load figures quoted are for guidance only. These chains are not tested.

## Mild Steel Welded Chains – DIN 5685

### SHORTER LINK – DIN 5685A

welded, untested



| Product Code | Size     | Wire Ø (mm) | Inside Link Length x Width (mm) | Weight per mtr (kgs) | *Maximum Load (kgs) |
|--------------|----------|-------------|---------------------------------|----------------------|---------------------|
| 883 06       | 2 x 16   | 2.0         | 16 x 4                          | 0.08                 | 25                  |
| 883 14       | 2.5 x 17 | 2.5         | 17 x 5                          | 0.11                 | 50                  |
| 883 20       | 3 x 16   | 3.0         | 16 x 6                          | 0.16                 | 85                  |
| 883 30       | 4 x 19   | 4.0         | 19 x 8                          | 0.30                 | 125                 |
| 883 40       | 5 x 21   | 5.0         | 21 x 10                         | 0.49                 | 170                 |
| 883 50       | 6 x 24   | 6.0         | 24 x 12                         | 0.68                 | 260                 |
| 883 62       | 7 x 28   | 7.0         | 28 x 14                         | 1.00                 | 385                 |
| 883 72       | 8 x 32   | 8.0         | 32 x 16                         | 1.31                 | 480                 |
| 883 80       | 10 x 40  | 10.0        | 40 x 20                         | 2.10                 | 685                 |
| 883 84       | 12 x 48  | 12.0        | 48 x 24                         | 2.94                 | 1100                |

**Finishes:** self colour; black; bright zinc; hot galvanised

**Supplied:** bulk in hanks; 10m boxes; 10m bags; on reels

\*Maximum load figures quoted are for guidance only. These chains are not tested.

### LONGER LINK – DIN 5685C

welded, untested



| Product Code | Size     | Wire Ø (mm) | Inside Link Length x Width (mm) | Weight per mtr (kgs) | *Maximum Load (kgs) |
|--------------|----------|-------------|---------------------------------|----------------------|---------------------|
| 883 08       | 2 x 22   | 2.0         | 22 x 4                          | 0.07                 | 25                  |
| 883 16       | 2.5 x 24 | 2.5         | 24 x 5                          | 0.11                 | 50                  |
| 883 26       | 3 x 26   | 3.0         | 26 x 6                          | 0.15                 | 80                  |
| 883 36       | 4 x 32   | 4.0         | 32 x 8                          | 0.26                 | 120                 |
| 883 46       | 5 x 35   | 5.0         | 35 x 10                         | 0.43                 | 160                 |
| 883 56       | 6 x 42   | 6.0         | 42 x 12                         | 0.57                 | 250                 |
| 883 68       | 7 x 49   | 7.0         | 49 x 14                         | 0.82                 | 370                 |
| 883 76       | 8 x 54   | 8.0         | 54 x 16                         | 1.03                 | 455                 |
| 883 82       | 10 x 66  | 10.0        | 66 x 20                         | 1.63                 | 650                 |
| 883 86       | 12 x 76  | 12.0        | 76 x 24                         | 2.63                 | 1020                |

**Finishes:** self colour; black; bright zinc; hot galvanised

**Supplied:** bulk in hanks; 10m boxes; 10m bags; on reels

\*Maximum load figures quoted are for guidance only. These chains are not tested.

## Mild Steel Welded Chains – Tested

### SHORT LINK CHAINS – DIN 766

welded, tested and certified



| Product Code | Size (mm) | Inside Link Length x Width (mm) | Weight per mtr (kg) | W. L. L. (kg) | Breaking Load (kg) |
|--------------|-----------|---------------------------------|---------------------|---------------|--------------------|
| 473 05       | 5         | 18.5 x 7                        | 0.50                | 250           | 1000               |
| 473 06       | 6         | 18.5 x 8                        | 0.75                | 350           | 1400               |
| 473 08       | 8         | 24 x 10                         | 1.35                | 630           | 2500               |
| 473 10       | 10        | 28 x 14                         | 2.30                | 1000          | 4000               |
| 473 12       | 12        | 36 x 17                         | 3.10                | 1360          | 5440               |
| 473 16       | 16        | 45 x 22                         | 5.80                | 2500          | 10000              |

**Finishes:** *self colour; bright zinc; hot galvanised*

**Supplied:** *bulk by the metre*

### LONG LINK CHAINS – DIN 763

welded, tested and certified



| Product Code | Size (mm) | Inside Link Length x Width (mm) | Weight per mtr (kg) | W. L. L. (kg) | Breaking Load (kg) |
|--------------|-----------|---------------------------------|---------------------|---------------|--------------------|
| 473 17       | 5         | 35 x 10                         | 0.43                | 200           | 800                |
| 473 19       | 6         | 42 x 12                         | 0.63                | 300           | 1200               |
| 473 23       | 8         | 54 x 16                         | 1.10                | 500           | 2000               |
| 473 25       | 10        | 66 x 20                         | 1.75                | 750           | 3000               |
| 473 27       | 12        | 78 x 24                         | 2.63                | 1120          | 4500               |
| 473 29       | 16        | 100 x 30                        | 4.45                | 2500          | 10000              |

**Finishes:** *self colour; bright zinc; hot galvanised*

**Supplied:** *bulk by the metre*

## Ess Hooks

mild steel

| Product Code | Size (mm) | Length (mm) | Inside Eye Ø (mm) |
|--------------|-----------|-------------|-------------------|
| 573 03       | 3         | 34          | 11                |
| 573 04       | 4         | 40          | 12                |
| 573 05       | 5         | 48          | 16                |
| 573 06       | 6         | 60          | 18                |
| 573 07       | 7         | 70          | 20                |
| 573 08       | 8         | 75          | 17                |



**Finish:** zinc plated  
**Supplied:** 3 - 6mm 50 per box  
 7 - 8mm 20 per box  
 bulk in 100s

## Repair Links

forged steel

| Product Code | Size (mm) | Inside Dims. (mm) |
|--------------|-----------|-------------------|
| 643 16       | 6         | 8 x 18            |
| 643 18       | 8         | 10 x 24           |
| 643 20       | 10        | 15 x 30           |



**Finish:** zinc plated  
**Supplied:** 10 per box  
 bulk in 100s

## Mending Links

mild steel

| Product Code | Size (mm) | Inside Dims. (mm) |
|--------------|-----------|-------------------|
| 643 03       | 3.5       | 22 x 7            |
| 643 04       | 4         | 24 x 7.5          |
| 643 05       | 5         | 28 x 9.5          |
| 643 06       | 6         | 32 x 12           |
| 643 07       | 7         | 36 x 14           |
| 643 08       | 8         | 40 x 17           |
| 643 10       | 10        | 51 x 23           |



**Finish:** zinc plated  
**Supplied:** 3.5 - 6mm 50 per box  
 7 - 10mm 20 per box  
 bulk in 100s

## Swivels

mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 773 04       | 4         | 47          |
| 773 05       | 5         | 67          |
| 773 06       | 6         | 74          |
| 773 07       | 7         | 81          |
| 773 08       | 8         | 96          |
| 773 10       | 10        | 106         |



**Finish:** zinc plated  
**Supplied:** 10 per box  
 bulk in 100s

## Quick Links

mild steel

| Product Code | Size (mm) | Inside Dims. (mm) |
|--------------|-----------|-------------------|
| 653 03       | 3.5       | 28 x 10           |
| 653 04       | 4         | 32 x 11           |
| 653 05       | 5         | 39 x 12           |
| 653 06       | 6         | 46 x 14           |
| 653 07       | 7         | 52 x 16           |
| 653 08       | 8         | 59 x 18           |
| 653 10       | 10        | 70 x 20           |
| 653 12       | 12        | 85 x 25           |
| 653 14       | 14        | 95 x 26           |
| 653 16       | 16        | 111 x 30          |



**Finish:** zinc plated  
**Supplied:** 3.5 - 6mm 10 per box  
 7 - 12mm 5 per box  
 bulk in 100s

## Welded Rings

mild steel

| Product Code | Size (mm) | Inside Ø (mm) |
|--------------|-----------|---------------|
| 663 03       | 3         | 20            |
| 663 04       | 4         | 25            |
| 663 05       | 5         | 30            |
| 663 06       | 6         | 35            |
| 663 07       | 7         | 40            |
| 663 08       | 8         | 45            |
| 663 10       | 10        | 50            |



**Finish:** zinc plated  
**Supplied:** 3 - 6mm 50 per box  
 7 - 10mm 20 per box  
 bulk in 100s

## Carbine Hooks

mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 563 04       | 4         | 40          |
| 563 05       | 5         | 50          |
| 563 06       | 6         | 60          |
| 563 07       | 7         | 70          |
| 563 08       | 8         | 80          |
| 563 10       | 10        | 100         |
| 563 11       | 11        | 120         |
| 563 12       | 12        | 140         |



**Finish:** zinc plated  
**Supplied:** 10 per box  
bulk in 100s

## Simplex Hooks

mild steel

| Product Code<br>No Swivel | Product Code<br>With Swivel | Length (mm) |
|---------------------------|-----------------------------|-------------|
| 583 30                    | 593 30                      | 30          |
| 583 35                    | 593 35                      | 35          |
| 583 40                    | 593 40                      | 40          |
| 583 50                    | 593 50                      | 50          |
| 583 60                    | 593 60                      | 60          |
| 583 70                    | 593 70                      | 70          |
| 583 80                    | 593 80                      | 80          |
| 583 90                    | 593 90                      | 90          |
| 583 92                    | 593 92                      | 100         |
| 583 94                    | 593 94                      | 120         |



**Finish:** zinc plated  
**Supplied:** 30 - 70mm 100 per box  
80 - 120mm 50 per box  
bulk in 1000s

## Carbine Hooks with Eye

mild steel

| Product Code | Size (mm) | Length (mm) | Inside Eye Ø (mm) |
|--------------|-----------|-------------|-------------------|
| 563 34       | 4         | 40          | 5.0               |
| 563 35       | 5         | 50          | 5.5               |
| 563 36       | 6         | 60          | 7.0               |
| 563 37       | 7         | 70          | 7.5               |
| 563 38       | 8         | 80          | 9.0               |
| 563 40       | 10        | 100         | 11.5              |



**Finish:** zinc plated  
**Supplied:** 10 per box  
bulk in 100s

## Springhooks to Crue

mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 603 50       | 5         | 50          |
| 603 63       | 6         | 65          |
| 603 75       | 7         | 70          |
| 603 88       | 8         | 80          |
| 603 90       | 9         | 90          |
| 603 91       | 10        | 105         |



**Finish:** zinc plated  
**Supplied:** 10 per box  
bulk in 100s

## Carbine Hooks with Safety Screw

mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 563 36       | 6         | 60          |
| 563 37       | 7         | 70          |
| 563 38       | 8         | 80          |
| 563 40       | 10        | 100         |



**Finish:** zinc plated  
**Supplied:** 10 per box  
bulk in 100s

## Springhooks to Swivel

mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 613 50       | 5         | 50          |
| 613 63       | 6         | 65          |
| 613 75       | 7         | 70          |
| 613 88       | 8         | 80          |
| 613 90       | 9         | 90          |
| 613 92       | 10        | 105         |



**Finish:** zinc plated  
**Supplied:** 10 per box  
bulk in 100s

## Swivel Snap Hooks

zinc diecast

| Product Code | Length (mm) | Inside Eye (mm) |
|--------------|-------------|-----------------|
| 636 62       | 62          | 10              |
| 636 77       | 77          | 10              |
| 636 80       | 80          | 16              |



**Finish:** nickel plated  
**Supplied:** 20 per box  
bulk in 100s

# Welded Chains & Accessories

## Dee Shackles

mild steel

| Product Code | Body & Pin size (mm) | Inside Length x Width (mm) |
|--------------|----------------------|----------------------------|
| 683 05       | 5                    | 19 x 10                    |
| 683 06       | 6                    | 25 x 13                    |
| 683 08       | 8                    | 30 x 16                    |
| 683 10       | 10                   | 38 x 19                    |
| 683 12       | 12                   | 49 x 25                    |
| 683 14       | 14                   | 56 x 29                    |
| 683 16       | 16                   | 65 x 32                    |
| 683 18       | 18                   | 69 x 38                    |
| 683 20       | 20                   | 71 x 37                    |
| 683 22       | 22                   | 84 x 43                    |
| 683 25       | 25                   | 95 x 50                    |



**Finish:** galvanised  
**Supplied:** 5 - 12mm 20 per box  
 14 - 25mm 10 per box  
 bulk in 100s

## Straining Screws – Eye/Eye

forged steel

| Product Code | Size (mm) | Body Length (mm) | Eye Ø (mm) |
|--------------|-----------|------------------|------------|
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |
|              |           |                  |            |

**Finish:** galvanised  
**Supplied:** 5 - 10mm 10 per box  
 12 - 25mm 5 per box  
 bulk in 100s

## Bow Shackles

mild steel

| Product Code | Body & Pin size (mm) | Inside Length x Width (mm) |
|--------------|----------------------|----------------------------|
| 673 05       | 5                    | 19 x 15                    |
| 673 06       | 6                    | 25 x 18                    |
| 673 08       | 8                    | 32 x 22                    |
| 673 10       | 10                   | 42 x 28                    |
| 673 12       | 12                   | 50 x 35                    |
| 673 14       | 14                   | 62 x 44                    |
| 673 16       | 16                   | 65 x 48                    |
| 673 19       | 18                   | 80 x 54                    |
| 673 20       | 20                   | 80 x 58                    |
| 673 22       | 22                   | 85 x 66                    |
| 673 25       | 25                   | 100 x 75                   |



**Finish:** galvanised  
**Supplied:** 5 - 12mm 20 per box  
 14 - 25mm 10 per box  
 bulk in 100s

## Straining Screws – Hook/Hook

forged steel

| Product Code | Size (mm) | Body Length (mm) | Inside Hook (mm) |
|--------------|-----------|------------------|------------------|
| 693 65       | 5         | 74               | 8                |
| 693 66       | 6         | 89               | 10               |
| 693 68       | 8         | 104              | 11               |
| 693 70       | 10        | 133              | 14               |
| 693 72       | 12        | 140              | 18               |
| 693 74       | 14        | 170              | 18               |
| 693 76       | 16        | 178              | 23               |
| 693 78       | 18        | 198              | 24.5             |
| 693 80       | 20        | 218              | 24.5             |
| 693 82       | 22        | 242              | 30               |
| 693 85       | 25        | 262              | 35               |





## Ringbolts - woodscrew thread mild steel

| Product Code | Size (mm) | Body Length (mm) | Ring (mm) |
|--------------|-----------|------------------|-----------|
| 803 06       | 6         | 40               | 6 x 35    |
| 803 08       | 8         | 50               | 8 x 40    |
| 803 10       | 10        | 70               | 10 x 45   |
| 803 12       | 12        | 80               | 12 x 50   |

Finish: zinc plated  
Supplied: 10 per box  
bulk in 100s



## Ringbolts with Nut mild steel

| Product Code | Size (mm) | Body Length (mm) | Ring (mm) |
|--------------|-----------|------------------|-----------|
| 803 16       | 6         | 80               | 6 x 35    |
| 803 18       | 8         | 90               | 8 x 40    |
| 803 20       | 10        | 80               | 10 x 50   |
| 803 22       | 10        | 100              | 10 x 50   |
| 803 24       | 12        | 100              | 10 x 50   |
| 803 26       | 12        | 120              | 10 x 50   |

Finish: zinc plated  
Supplied: 10 per box  
bulk in 100s



## Swing Hooks - woodscrew thread mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 803 30       | 9         | 120         |

Finish: zinc plated  
Supplied: 10 per box  
bulk in 100s



## Swing Hooks with Nut mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 803 40       | 12        | 70          |
| 803 42       | 12        | 150         |
| 803 44       | 14        | 80          |
| 803 46       | 14        | 180         |

Finish: zinc plated  
Supplied: 10 per box  
bulk in 100s



## Spiked Chain mild steel

| Product Code | Type           | Size (mm) | Inside Dims. (mm) |
|--------------|----------------|-----------|-------------------|
| 513 02       | Every Link     | 6         | 50 x 13           |
| 513 12       | Alternate Link | 6         | 50 x 13           |

Finish: galvanised; black  
Supplied: 25m hanks



## Hook on Plate mild steel

| Product Code | Type     | Plate (mm) |
|--------------|----------|------------|
| 513 24       | 8mm Hook | 50 x 50    |

Finish: galvanised; black  
Supplied: 10 per box  
bulk in 100s



## Staple on Plate mild steel

| Product Code | Type       | Plate (mm) |
|--------------|------------|------------|
| 513 22       | 6mm Staple | 50 x 50    |

Finish: galvanised; black  
Supplied: 10 per box  
bulk in 100s



## Ring on Plate mild steel

| Product Code | Plate (mm) |
|--------------|------------|
| 513 52       | 50 x 50    |


Finish: galvanised; black  
Supplied: 10 per box  
bulk in 100s



## Fittings for 4" posts mild steel

| Product Code | Type              | Plate (mm) |
|--------------|-------------------|------------|
| 513 32       | Intermediate Post | 10         |
| 513 42       | End Post          | 10         |

Finish: galvanised  
Supplied: 10 per box  
bulk in 100s





# Welded Chains & Accessories



## Unwelded Eyebolts (inc. nut & washer) mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 783 30       | 6         | 100         |
| 783 31       | 6         | 150         |
| 783 60       | 8         | 100         |
| 783 61       | 8         | 150         |
| 783 62       | 8         | 200         |
| 783 64       | 8         | 250         |
| 783 81       | 10        | 150         |
| 783 82       | 10        | 200         |
| 783 84       | 10        | 250         |
| 783 85       | 10        | 300         |

**Finish:** zinc plated  
**Supplied:** 50 per box  
bulk in 100s



## Lynch Pins mild steel

| Product Code | Pin Size (mm) | Inside Ring Ø (mm) |
|--------------|---------------|--------------------|
| 523 14       | 4.5           | 41                 |
| 523 16       | 6             | 41                 |
| 523 17       | 6             | 45                 |
| 523 19       | 7             | 41                 |
| 523 21       | 8             | 41                 |
| 523 22       | 8             | 45                 |
| 523 24       | 9             | 41                 |
| 523 26       | 10            | 41                 |
| 523 28       | 11            | 41                 |
| 523 29       | 11            | 45                 |

**Finish:** zinc plated  
**Supplied:** 25 per box  
bulk in 100s



## Welded Eyebolts (inc. nut & washer) mild steel

| Product Code | Size (mm) | Length (mm) |
|--------------|-----------|-------------|
| 793 30       | 6         | 100         |
| 793 31       | 6         | 150         |
| 793 60       | 8         | 100         |
| 793 61       | 8         | 150         |
| 793 62       | 8         | 200         |
| 793 64       | 8         | 250         |
| 793 81       | 10        | 150         |
| 793 82       | 10        | 200         |
| 793 84       | 10        | 250         |
| 793 85       | 10        | 300         |

**Finish:** zinc plated  
**Supplied:** 50 per box  
bulk in 100s



## Lifting Eyebolts (DIN 580) forged steel

| Product Code | Size (mm) | Inside Ø (mm) |
|--------------|-----------|---------------|
| 703 06       | M6        | 20            |
| 703 08       | M8        | 20            |
| 703 10       | M10       | 25            |
| 703 12       | M12       | 30            |
| 703 14       | M14       | 35            |
| 703 16       | M16       | 35            |
| 703 18       | M18       | 38            |
| 703 20       | M20       | 40            |
| 703 22       | M22       | 47            |
| 703 24       | M24       | 50            |

**Finishes:** self colour; zinc plated  
**Supplied:** 6 - 14mm 10 per box  
16 - 24mm 5 per box  
bulk in 100s



## Spring Cotter Pins mild steel

| Product Code | Wire Size (mm) | Length (mm) |
|--------------|----------------|-------------|
| 523 32       | 2              | 57          |
| 523 33       | 3              | 72          |
| 523 34       | 4              | 74          |
| 523 35       | 5              | 102         |
| 523 36       | 6              | 126         |

**Finish:** zinc plated  
**Supplied:** 100 per box  
bulk in 1000s



## Lifting Eynuts (DIN 582) forged steel

| Product Code | Size (mm) | Inside Ø (mm) |
|--------------|-----------|---------------|
| 713 06       | M6        | 20            |
| 713 08       | M8        | 20            |
| 713 10       | M10       | 25            |
| 713 12       | M12       | 30            |
| 713 14       | M14       | 30            |
| 713 16       | M16       | 35            |
| 713 18       | M18       | 38            |
| 713 20       | M20       | 40            |
| 713 22       | M22       | 47            |
| 713 24       | M24       | 50            |

**Finishes:** self colour; zinc plated  
**Supplied:** 6 - 14mm 10 per box  
16 - 24mm 5 per box  
bulk in 100s



# Welded Chains & Accessories



## Wire Rope Grips - Simplex mild steel

| Product Code | Size (mm) | Thread | Length x Width (mm) |
|--------------|-----------|--------|---------------------|
| 723 72       | 2         | M4     | 15 x 4              |
| 723 73       | 3         | M4     | 17 x 6              |
| 723 74       | 4         | M5     | 20 x 8              |
| 723 75       | 5         | M5     | 25 x 10             |
| 723 76       | 6         | M6     | 30 x 12             |
| 723 78       | 8         | M8     | 37 x 17             |



**Finish:** zinc plated  
**Supplied:** 2 - 4mm 100 per box  
5 - 8mm 50 per box  
bulk in 100s

## Commercial Wire Rope Thimbles mild steel

| Product Code | Size (mm) | Length x Width x Thickness (mm) |
|--------------|-----------|---------------------------------|
| 733 03       | 3         | 24 x 16 x 5                     |
| 733 04       | 4         | 28 x 19 x 6                     |
| 733 05       | 5         | 35 x 22 x 7                     |
| 733 06       | 6         | 40 x 27 x 9                     |
| 733 08       | 8         | 49 x 31 x 12                    |
| 733 10       | 10        | 55 x 34 x 14                    |
| 733 12       | 12        | 66 x 42 x 16                    |
| 733 14       | 14        | 78 x 48 x 19                    |
| 733 16       | 16        | 90 x 55 x 21                    |
| 733 18       | 18        | 100 x 65 x 23                   |
| 733 20       | 20        | 115 x 70 x 29                   |
| 733 22       | 22        | 118 x 80 x 30                   |
| 733 24       | 24        | 130 x 85 x 33                   |



**Finish:** galvanised  
**Supplied:** 3 - 12mm 20 per box  
14 - 24mm 10 per box  
bulk in 100s

## Wire Rope Grips - Duplex mild steel


| Product Code | Size (mm) | Thread | Length x Width (mm) |
|--------------|-----------|--------|---------------------|
| 723 82       | 2         | M4     | 30 x 4              |
| 723 83       | 3         | M4     | 35 x 6              |
| 723 84       | 4         | M5     | 40 x 8              |
| 723 85       | 5         | M5     | 50 x 10             |
| 723 86       | 6         | M6     | 60 x 12             |
| 723 88       | 8         | M8     | 75 x 15             |



**Finish:** zinc plated  
**Supplied:** 2 - 4mm 100 per box  
5 - 8mm 50 per box  
bulk in 100s

## Wire Rope galvanised steel

| Product Code | Size Ø (mm) |
|--------------|-------------|
| 893 50       | 1.5         |
| 893 51       | 2           |
| 893 52       | 2.5         |
| 893 53       | 3           |
| 893 55       | 4           |
| 893 57       | 5           |
| 893 59       | 6           |
| 893 61       | 8           |



(7 x 7 Steel Core)

**Finish:** galvanised  
**Supplied:** bulk on reels


## Commercial Wire Rope Grips (DIN 741) mild steel

| Product Code | Size (mm) | Length x Width x Thickness (mm) |
|--------------|-----------|---------------------------------|
| 723 03       | 3         | 21 x 21 x 10                    |
| 723 05       | 5         | 24 x 22 x 11                    |
| 723 06       | 6         | 28 x 24 x 12                    |
| 723 08       | 8         | 35 x 30 x 14                    |
| 723 10       | 10        | 42 x 34 x 18                    |
| 723 12       | 12        | 56 x 40 x 23                    |
| 723 14       | 14        | 58 x 44 x 24                    |
| 723 16       | 16        | 63 x 50 x 26                    |
| 723 20       | 20        | 75 x 53 x 28                    |
| 723 22       | 22        | 82 x 60 x 33                    |
| 723 24       | 24        | 95 x 66 x 36                    |



**Finish:** galvanised  
**Supplied:** 3 - 12mm 20 per box  
14 - 24mm 10 per box  
bulk in 100s


| Product Code | Size Ø (mm) |
|--------------|-------------|
| 893 74       | 2           |
| 893 75       | 3           |
| 893 76       | 4           |
| 893 77       | 5           |
| 893 78       | 6           |
| 893 79       | 8           |



(6 x 19 Fibre Core)

**Finish:** galvanised  
**Supplied:** bulk on reels

| Product Code | Size Ø (mm) |
|--------------|-------------|
| 893 85       | 3           |
| 893 87       | 4           |
| 893 89       | 5           |
| 893 91       | 6           |
| 893 93       | 8           |



(7 x 19 Steel Core)

**Finish:** galvanised  
**Supplied:** bulk on reels