







Pos	A	B	C
4	7.00	3.81	5.60
6	9.54	6.35	8.14
8	12.08	8.89	10.68
10	14.62	11.43	13.22
12	17.16	13.97	15.76
14	19.70	16.51	18.30
16	22.24	19.05	20.84
18	24.78	21.59	23.38
20	27.32	24.13	25.92
22	29.86	26.67	28.46
24	32.40	29.21	31.00
26	34.94	31.75	33.54



Specifications:
 Current rating: 1.0A AC, DC
 Voltage rating: 30V AC, DC
 Contact resistance: 20m ohm Max
 Insulation resistance: 1000M ohm Min
 Withstanding voltage: AC 500V AC/minute
 Operating Temperature: -40°C ~ +105°C
 Materials:
 Insulator: High Temp Plastic UL94V-0
 Contact material: Phosphor Bronze
 Finish: Tin Plated

How to Order

TMM-X-X-XX-X

Type

- 1-IDC Male
- 2-IDC Plug
- 3-DIP Male Straight
- 4-DIP Female Straight
- 5-DIP Female R/A
- 6-SMT Female Straight


Locking System

- 0-without lock
- L-with lock

Packaging

- 1 - Tape & Reel
- 2 - Tube
- 3 - Bag

Number of Positions
 04, 06, 08, 10, 12,
 14, 16, 18 or 20



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE		AMPHENOL Amphenol European Design Center	
X, ±0.3	DRAWN Stephane	2006/04/22	Micro Match Dip type Female		Scale N.A. Sheet 1 of 1	
X.X ±0.1	CHECKED Rob K.	2006/04/23				
X.XX ±0.05	APPROVED Rob K.	2006/04/23				
UNLESS OTHERWISE SPECIFIED		UNIT : MM	SIZE: A4	DRAWING N°	TMM-4-0-XX-X	
						REV