


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0008340105
Status: Active
Overview: kk
Description: KK® Crimp Terminal, Series 1799, Female, with Selective Gold (Au) Plated Brass Contact, 18-24 AWG, Chain on Reel

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PSX-08-30 \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	1799
Application	Power
Crimp Quality Equipment	Yes
Overview	kk
Product Name	KK®
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	7A
Voltage - Maximum	250V
Material Info	
Old Part Number	1799-MAG1
Reference - Drawing Numbers	
Product Specification	PSX-08-30
Sales Drawing	SD-1799-MA



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
1799Series

Mates With
2139 Crimp Housing

Use With
41696 Crimp Housings

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Extraction Tool	0011030003
Mini-Mac™	0011182130
Applicator	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION