

Part 2502-20J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	680 μ H	
Tolerance	± 5	
Q		
SRF	3.4 MHz	
DCR	10.5 Ω	
Max Current	97 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-52H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3300 μ H	
Tolerance	± 3	
Q		
SRF	1.6 MHz	
DCR	38 Ω	
Max Current	61 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-52G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3300 μ H	
Tolerance	± 2	
Q		
SRF	1.6 MHz	
DCR	38 Ω	
Max Current	61 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-52F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3300 μ H	
Tolerance	± 1	
Q		
SRF	1.6 MHz	
DCR	38 Ω	
Max Current	61 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-50J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3000 μ H	
Tolerance	± 5	
Q		
SRF	1.7 MHz	
DCR	35 Ω	
Max Current	63 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-50H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3000 μ H	
Tolerance	± 3	
Q		
SRF	1.7 MHz	
DCR	35 Ω	
Max Current	63 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-50G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3000 μ H	
Tolerance	± 2	
Q		
SRF	1.7 MHz	
DCR	35 Ω	
Max Current	63 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-52J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3300 μ H	
Tolerance	± 5	
Q		
SRF	1.6 MHz	
DCR	38 Ω	
Max Current	61 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-48J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2700 μ H	
Tolerance	± 5	
Q		
SRF	1.8 MHz	
DCR	33 Ω	
Max Current	65 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-56G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	3900 μ H	
Tolerance	± 2	
Q		
SRF	1.45 MHz	
DCR	44 Ω	
Max Current	62 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-50F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3000 μ H	
Tolerance	± 1	
Q		
SRF	1.7 MHz	
DCR	35 Ω	
Max Current	63 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-54F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3600 μ H	
Tolerance	± 1	
Q		
SRF	1.5 MHz	
DCR	40 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-54G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3600 μ H	
Tolerance	± 2	
Q		
SRF	1.5 MHz	
DCR	40 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-54H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3600 μ H	
Tolerance	± 3	
Q		
SRF	1.5 MHz	
DCR	40 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-58F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4300 μ H	
Tolerance	± 1	
Q		
SRF	1.4 MHz	
DCR	46 Ω	
Max Current	60 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-56F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	3900 μ H	
Tolerance	± 1	
Q		
SRF	1.45 MHz	
DCR	44 Ω	
Max Current	62 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-56H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	3900 μ H	
Tolerance	± 3	
Q		
SRF	1.45 MHz	
DCR	44 Ω	
Max Current	62 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-56J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	3900 μ H	
Tolerance	± 5	
Q		
SRF	1.45 MHz	
DCR	44 Ω	
Max Current	62 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-48H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2700 μ H	
Tolerance	± 3	
Q		
SRF	1.8 MHz	
DCR	33 Ω	
Max Current	65 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-42J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2000 μ H	
Tolerance	± 5	
Q		
SRF	2.1 MHz	
DCR	29 Ω	
Max Current	69 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-54J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	3600 μ H	
Tolerance	± 5	
Q		
SRF	1.5 MHz	
DCR	40 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-44F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2200 μ H	
Tolerance	± 1	
Q		
SRF	2 MHz	
DCR	30 Ω	
Max Current	68 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-38J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1600 μ H	
Tolerance	± 5	
Q		
SRF	2.3 MHz	
DCR	26 Ω	
Max Current	74 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-40F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1800 μ H	
Tolerance	± 1	
Q		
SRF	2.2 MHz	
DCR	28 Ω	
Max Current	71 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-40G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1800 μ H	
Tolerance	± 2	
Q		
SRF	2.2 MHz	
DCR	28 Ω	
Max Current	71 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-40H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1800 μ H	
Tolerance	± 3	
Q		
SRF	2.2 MHz	
DCR	28 Ω	
Max Current	71 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-40J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1800 μ H	
Tolerance	± 5	
Q		
SRF	2.2 MHz	
DCR	28 Ω	
Max Current	71 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-42F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2000 μ H	
Tolerance	± 1	
Q		
SRF	2.1 MHz	
DCR	29 Ω	
Max Current	69 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Unable to Serve this Request

Site temporarily unavailable.

Connection timed out - please try again.

Part 2502-44G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2200 μ H	
Tolerance	± 2	
Q		
SRF	2 MHz	
DCR	30 Ω	
Max Current	68 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-63G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5100 μ H	
Tolerance	± 2	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-48G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2700 μ H	
Tolerance	± 2	
Q		
SRF	1.8 MHz	
DCR	33 Ω	
Max Current	65 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-58G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4300 μ H	
Tolerance	± 2	
Q		
SRF	1.4 MHz	
DCR	46 Ω	
Max Current	60 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-44H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2200 μ H	
Tolerance	± 3	
Q		
SRF	2 MHz	
DCR	30 Ω	
Max Current	68 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-44J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2200 μ H	
Tolerance	± 5	
Q		
SRF	2 MHz	
DCR	30 Ω	
Max Current	68 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-46F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2400 μ H	
Tolerance	± 1	
Q		
SRF	1.9 MHz	
DCR	31 Ω	
Max Current	67 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-46G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2400 μ H	
Tolerance	± 2	
Q		
SRF	1.9 MHz	
DCR	31 Ω	
Max Current	67 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-46H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2400 μ H	
Tolerance	± 3	
Q		
SRF	1.9 MHz	
DCR	31 Ω	
Max Current	67 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-46J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2400 μ H	
Tolerance	± 5	
Q		
SRF	1.9 MHz	
DCR	31 Ω	
Max Current	67 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-48F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2700 μ H	
Tolerance	± 1	
Q		
SRF	1.8 MHz	
DCR	33 Ω	
Max Current	65 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-42H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	2000 μ H	
Tolerance	± 3	
Q		
SRF	2.1 MHz	
DCR	29 Ω	
Max Current	69 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-72J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	8200 μ H	
Tolerance	± 5	
Q		
SRF	1.05 MHz	
DCR	65 Ω	
Max Current	51 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-68H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6800 μ H	
Tolerance	± 3	
Q		
SRF	1.15 MHz	
DCR	59 Ω	
Max Current	54 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-68J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6800 μ H	
Tolerance	± 5	
Q		
SRF	1.15 MHz	
DCR	59 Ω	
Max Current	54 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-70F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	7500 μ H	
Tolerance	± 1	
Q		
SRF	1.1 MHz	
DCR	72 Ω	
Max Current	52 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-70G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	7500 μ H	
Tolerance	± 2	
Q		
SRF	1.1 MHz	
DCR	72 Ω	
Max Current	52 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-70H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	7500 μ H	
Tolerance	± 3	
Q		
SRF	1.1 MHz	
DCR	72 Ω	
Max Current	52 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-70J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	7500 μ H	
Tolerance	± 5	
Q		
SRF	1.1 MHz	
DCR	72 Ω	
Max Current	52 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-72F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	8200 μ H	
Tolerance	± 1	
Q		
SRF	1.05 MHz	
DCR	65 Ω	
Max Current	51 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-62H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5000 μ H	
Tolerance	± 3	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-72H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	8200 μ H	
Tolerance	± 3	
Q		
SRF	1.05 MHz	
DCR	65 Ω	
Max Current	51 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-66J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6200 μ H	
Tolerance	± 5	
Q		
SRF	1.2 MHz	
DCR	56 Ω	
Max Current	55 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-74F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	9100 μ H	
Tolerance	± 1	
Q		
SRF	1 MHz	
DCR	68 Ω	
Max Current	49 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-74G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	9100 μ H	
Tolerance	± 2	
Q		
SRF	1 MHz	
DCR	68 Ω	
Max Current	49 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-74H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	9100 μ H	
Tolerance	± 3	
Q		
SRF	1 MHz	
DCR	68 Ω	
Max Current	49 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-74J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	9100 μ H	
Tolerance	± 5	
Q		
SRF	1 MHz	
DCR	68 Ω	
Max Current	49 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-76F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	10000 μ H	
Tolerance	± 1	
Q		
SRF	0.95 MHz	
DCR	72 Ω	
Max Current	48 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-76G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	10000 μ H	
Tolerance	± 2	
Q		
SRF	0.95 MHz	
DCR	72 Ω	
Max Current	48 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-76H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	10000 μ H	
Tolerance	± 3	
Q		
SRF	0.95 MHz	
DCR	72 Ω	
Max Current	48 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-76J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	10000 μ H	
Tolerance	± 5	
Q		
SRF	0.95 MHz	
DCR	72 Ω	
Max Current	48 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-72G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	8200 μ H	
Tolerance	± 2	
Q		
SRF	1.05 MHz	
DCR	65 Ω	
Max Current	51 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-63J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5100 μ H	
Tolerance	± 5	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-58J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4300 μ H	
Tolerance	± 5	
Q		
SRF	1.4 MHz	
DCR	46 Ω	
Max Current	60 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-60F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4700 μ H	
Tolerance	± 1	
Q		
SRF	1.35 MHz	
DCR	48 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-60G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4700 μ H	
Tolerance	± 2	
Q		
SRF	1.35 MHz	
DCR	48 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-60H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4700 μ H	
Tolerance	± 3	
Q		
SRF	1.35 MHz	
DCR	48 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-60J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4700 μ H	
Tolerance	± 5	
Q		
SRF	1.35 MHz	
DCR	48 Ω	
Max Current	59 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-62F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5000 μ H	
Tolerance	± 1	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-62G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5000 μ H	
Tolerance	± 2	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-38H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1600 μ H	
Tolerance	± 3	
Q		
SRF	2.3 MHz	
DCR	26 Ω	
Max Current	74 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-68G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6800 μ H	
Tolerance	± 2	
Q		
SRF	1.15 MHz	
DCR	59 Ω	
Max Current	54 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-63F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5100 μ H	
Tolerance	± 1	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-68F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6800 μ H	
Tolerance	± 1	
Q		
SRF	1.15 MHz	
DCR	59 Ω	
Max Current	54 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-64F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5600 μ H	
Tolerance	± 1	
Q		
SRF	1.25 MHz	
DCR	53 Ω	
Max Current	56 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-64G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5600 μ H	
Tolerance	± 2	
Q		
SRF	1.25 MHz	
DCR	53 Ω	
Max Current	56 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-64H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5600 μ H	
Tolerance	± 3	
Q		
SRF	1.25 MHz	
DCR	53 Ω	
Max Current	56 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-64J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5600 μ H	
Tolerance	± 5	
Q		
SRF	1.25 MHz	
DCR	53 Ω	
Max Current	56 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-66F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6200 μ H	
Tolerance	± 1	
Q		
SRF	1.2 MHz	
DCR	56 Ω	
Max Current	55 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-66G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6200 μ H	
Tolerance	± 2	
Q		
SRF	1.2 MHz	
DCR	56 Ω	
Max Current	55 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-66H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	6200 μ H	
Tolerance	± 3	
Q		
SRF	1.2 MHz	
DCR	56 Ω	
Max Current	55 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-58H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	4300 μ H	
Tolerance	± 3	
Q		
SRF	1.4 MHz	
DCR	46 Ω	
Max Current	60 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-62J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5000 μ H	
Tolerance	± 5	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-14H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	500 μ H	
Tolerance	± 3	
Q		
SRF	3.7 MHz	
DCR	11.3 Ω	
Max Current	106 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-10G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	430 μ H	
Tolerance	± 2	
Q		
SRF	4.3 MHz	
DCR	10.6 Ω	
Max Current	111 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-10H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	430 μ H	
Tolerance	± 3	
Q		
SRF	4.3 MHz	
DCR	10.6 Ω	
Max Current	111 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-10J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	430 μ H	
Tolerance	± 5	
Q		
SRF	4.3 MHz	
DCR	10.6 Ω	
Max Current	111 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-12F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	470 μ H	
Tolerance	± 1	
Q		
SRF	4 MHz	
DCR	11 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-12G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	470 μ H	
Tolerance	± 2	
Q		
SRF	4 MHz	
DCR	11 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-12H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	470 μ H	
Tolerance	± 3	
Q		
SRF	4 MHz	
DCR	11 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-12J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	470 μ H	
Tolerance	± 5	
Q		
SRF	4 MHz	
DCR	11 Ω	
Max Current	108 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-16J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	560 μ H	
Tolerance	± 5	
Q		
SRF	3.6 MHz	
DCR	12.3 Ω	
Max Current	104 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-14G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	500 μ H	
Tolerance	± 2	
Q		
SRF	3.7 MHz	
DCR	11.3 Ω	
Max Current	106 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-08H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	390 μ H	
Tolerance	± 3	
Q		
SRF	4.5 MHz	
DCR	10 Ω	
Max Current	114 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-14J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	500 μ H	
Tolerance	± 5	
Q		
SRF	3.7 MHz	
DCR	11.3 Ω	
Max Current	106 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-15F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	510 μ H	
Tolerance	± 1	
Q		
SRF	3.8 MHz	
DCR	11.6 Ω	
Max Current	105 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-15G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	510 μ H	
Tolerance	± 2	
Q		
SRF	3.8 MHz	
DCR	11.6 Ω	
Max Current	105 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-15H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	510 μ H	
Tolerance	± 3	
Q		
SRF	3.8 MHz	
DCR	11.6 Ω	
Max Current	105 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-15J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	510 μ H	
Tolerance	± 5	
Q		
SRF	3.8 MHz	
DCR	11.6 Ω	
Max Current	105 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-16F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	560 μ H	
Tolerance	± 1	
Q		
SRF	3.6 MHz	
DCR	12.3 Ω	
Max Current	104 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-16G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	560 μ H	
Tolerance	± 2	
Q		
SRF	3.6 MHz	
DCR	12.3 Ω	
Max Current	104 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-16H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	560 μ H	
Tolerance	± 3	
Q		
SRF	3.6 MHz	
DCR	12.3 Ω	
Max Current	104 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-14F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	500 μ H	
Tolerance	± 1	
Q		
SRF	3.7 MHz	
DCR	11.3 Ω	
Max Current	106 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-04F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	330 μ H	
Tolerance	± 1	
Q		
SRF	5 MHz	
DCR	9.1 Ω	
Max Current	120 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-63H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.74 inches	
Width	0.24 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	2.5 grams	
Inductance	5100 μ H	
Tolerance	± 3	
Q		
SRF	1.3 MHz	
DCR	50 Ω	
Max Current	58 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-38G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1600 μ H	
Tolerance	± 2	
Q		
SRF	2.3 MHz	
DCR	26 Ω	
Max Current	74 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-00F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	270 μ H	
Tolerance	± 1	
Q		
SRF	5.6 MHz	
DCR	8.2 Ω	
Max Current	126 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-00G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	270 μ H	
Tolerance	± 2	
Q		
SRF	5.6 MHz	
DCR	8.2 Ω	
Max Current	126 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-00H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	270 μ H	
Tolerance	± 3	
Q		
SRF	5.6 MHz	
DCR	8.2 Ω	
Max Current	126 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-00J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	270 μ H	
Tolerance	± 5	
Q		
SRF	5.6 MHz	
DCR	8.2 Ω	
Max Current	126 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-02F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	300 μ H	
Tolerance	± 1	
Q		
SRF	5.3 MHz	
DCR	8.7 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-02G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	300 μ H	
Tolerance	± 2	
Q		
SRF	5.3 MHz	
DCR	8.7 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-10F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	430 μ H	
Tolerance	± 1	
Q		
SRF	4.3 MHz	
DCR	10.6 Ω	
Max Current	111 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-02J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	300 μ H	
Tolerance	± 5	
Q		
SRF	5.3 MHz	
DCR	8.7 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-08J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	390 μ H	
Tolerance	± 5	
Q		
SRF	4.5 MHz	
DCR	10 Ω	
Max Current	114 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-04G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	330 μ H	
Tolerance	± 2	
Q		
SRF	5 MHz	
DCR	9.1 Ω	
Max Current	120 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-04J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	330 μ H	
Tolerance	± 5	
Q		
SRF	5 MHz	
DCR	9.1 Ω	
Max Current	120 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-06G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	360 μ H	
Tolerance	± 2	
Q		
SRF	4.7 MHz	
DCR	9.6 Ω	
Max Current	115 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-06H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	360 μ H	
Tolerance	± 3	
Q		
SRF	4.7 MHz	
DCR	9.6 Ω	
Max Current	115 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-06J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	360 μ H	
Tolerance	± 5	
Q		
SRF	4.7 MHz	
DCR	9.6 Ω	
Max Current	115 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-08F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	390 μ H	
Tolerance	± 1	
Q		
SRF	4.5 MHz	
DCR	10 Ω	
Max Current	114 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-08G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	390 μ H	
Tolerance	± 2	
Q		
SRF	4.5 MHz	
DCR	10 Ω	
Max Current	114 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-06F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	360 μ H	
Tolerance	± 1	
Q		
SRF	4.7 MHz	
DCR	9.6 Ω	
Max Current	115 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-02H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	300 μ H	
Tolerance	± 3	
Q		
SRF	5.3 MHz	
DCR	8.7 Ω	
Max Current	122 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-34F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1300 μ H	
Tolerance	± 1	
Q		
SRF	2.6 MHz	
DCR	23 Ω	
Max Current	78 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-28G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	1000 μ H	
Tolerance	± 2	
Q		
SRF	2.8 MHz	
DCR	13.5 Ω	
Max Current	88 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-28H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	1000 μ H	
Tolerance	± 3	
Q		
SRF	2.8 MHz	
DCR	13.5 Ω	
Max Current	88 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-28J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	1000 μ H	
Tolerance	± 5	
Q		
SRF	2.8 MHz	
DCR	13.5 Ω	
Max Current	88 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-30F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1100 μ H	
Tolerance	± 1	
Q		
SRF	2.8 MHz	
DCR	21 Ω	
Max Current	81 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-30G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1100 μ H	
Tolerance	± 2	
Q		
SRF	2.8 MHz	
DCR	21 Ω	
Max Current	81 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-30H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1100 μ H	
Tolerance	± 3	
Q		
SRF	2.8 MHz	
DCR	21 Ω	
Max Current	81 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-30J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1100 μ H	
Tolerance	± 5	
Q		
SRF	2.8 MHz	
DCR	21 Ω	
Max Current	81 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-32F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1200 μ H	
Tolerance	± 1	
Q		
SRF	2.7 MHz	
DCR	22 Ω	
Max Current	79 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-28F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	1000 μ H	
Tolerance	± 1	
Q		
SRF	2.8 MHz	
DCR	13.5 Ω	
Max Current	88 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-32H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1200 μ H	
Tolerance	± 3	
Q		
SRF	2.7 MHz	
DCR	22 Ω	
Max Current	79 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-32J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1200 μ H	
Tolerance	± 5	
Q		
SRF	2.7 MHz	
DCR	22 Ω	
Max Current	79 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-34H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1300 μ H	
Tolerance	± 3	
Q		
SRF	2.6 MHz	
DCR	23 Ω	
Max Current	78 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-34J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1300 μ H	
Tolerance	± 5	
Q		
SRF	2.6 MHz	
DCR	23 Ω	
Max Current	78 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-36F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1500 μ H	
Tolerance	± 1	
Q		
SRF	2.4 MHz	
DCR	25 Ω	
Max Current	76 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-36G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1500 μ H	
Tolerance	± 2	
Q		
SRF	2.4 MHz	
DCR	25 Ω	
Max Current	76 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-36H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1500 μ H	
Tolerance	± 3	
Q		
SRF	2.4 MHz	
DCR	25 Ω	
Max Current	76 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-18F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	620 μ H	
Tolerance	± 1	
Q		
SRF	3.5 MHz	
DCR	9.9 Ω	
Max Current	101 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-04H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	330 μ H	
Tolerance	± 3	
Q		
SRF	5 MHz	
DCR	9.1 Ω	
Max Current	120 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-36J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1500 μ H	
Tolerance	± 5	
Q		
SRF	2.4 MHz	
DCR	25 Ω	
Max Current	76 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-38F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1600 μ H	
Tolerance	± 1	
Q		
SRF	2.3 MHz	
DCR	26 Ω	
Max Current	74 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-32G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1200 μ H	
Tolerance	± 2	
Q		
SRF	2.7 MHz	
DCR	22 Ω	
Max Current	79 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-22G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	750 μ H	
Tolerance	± 2	
Q		
SRF	3.3 MHz	
DCR	11.5 Ω	
Max Current	95 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-18J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	620 μ H	
Tolerance	± 5	
Q		
SRF	3.5 MHz	
DCR	9.9 Ω	
Max Current	101 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-20F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	680 μ H	
Tolerance	± 1	
Q		
SRF	3.4 MHz	
DCR	10.5 Ω	
Max Current	97 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-18H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	620 μ H	
Tolerance	± 3	
Q		
SRF	3.5 MHz	
DCR	9.9 Ω	
Max Current	101 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-34G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.56 inches	
Width	0.215 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	1.5 grams	
Inductance	1300 μ H	
Tolerance	± 2	
Q		
SRF	2.6 MHz	
DCR	23 Ω	
Max Current	78 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-26J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	910 μ H	
Tolerance	± 5	
Q		
SRF	2.9 MHz	
DCR	12.8 Ω	
Max Current	91 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-18G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	620 μ H	
Tolerance	± 2	
Q		
SRF	3.5 MHz	
DCR	9.9 Ω	
Max Current	101 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-20G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	680 μ H	
Tolerance	± 2	
Q		
SRF	3.4 MHz	
DCR	10.5 Ω	
Max Current	97 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-20H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	680 μ H	
Tolerance	± 3	
Q		
SRF	3.4 MHz	
DCR	10.5 Ω	
Max Current	97 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Unable to Serve this Request

Site temporarily unavailable.

Connection timed out - please try again.

Part 2502-22H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	750 μ H	
Tolerance	± 3	
Q		
SRF	3.3 MHz	
DCR	11.5 Ω	
Max Current	95 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-24G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	820 μ H	
Tolerance	± 2	
Q		
SRF	3.1 MHz	
DCR	12.1 Ω	
Max Current	92 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Unable to Serve this Request

Site temporarily unavailable.

Connection timed out - please try again.

Part 2502-26G		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	910 μ H	
Tolerance	± 2	
Q		
SRF	2.9 MHz	
DCR	12.8 Ω	
Max Current	91 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-22J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	750 μ H	
Tolerance	± 5	
Q		
SRF	3.3 MHz	
DCR	11.5 Ω	
Max Current	95 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-26F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	910 μ H	
Tolerance	± 1	
Q		
SRF	2.9 MHz	
DCR	12.8 Ω	
Max Current	91 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-24J		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	820 μ H	
Tolerance	± 5	
Q		
SRF	3.1 MHz	
DCR	12.1 Ω	
Max Current	92 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-24F		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	820 μ H	
Tolerance	± 1	
Q		
SRF	3.1 MHz	
DCR	12.1 Ω	
Max Current	92 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Part 2502-24H		Check Stock
Series	2502	
Type	RF Inductors	
Description	Molded Unshielded RF Coil	
Mounting	Through Hole	
Shielded	No	
QPL	No	
COTS	No	
ROHS	No	
MIL No.	Not Applicable	
Length	0.44 inches	
Width	0.19 inches	
Height	inches	
Lead Length	1.44 inches	
Weight	0.95 grams	
Inductance	820 μ H	
Tolerance	± 3	
Q		
SRF	3.1 MHz	
DCR	12.1 Ω	
Max Current	92 mA	
Inc Current		
Inc Current %		
Ind Test Freq	0.1 MHz	
Q Test Freq	0.1 MHz	
Core	Ferrite	
Sleeve	Not Applicable	

Parts

2502-00F Molded Unshielded RF Coil
 2502-00G Molded Unshielded RF Coil
 2502-00H Molded Unshielded RF Coil
 2502-00J Molded Unshielded RF Coil
 2502-02F Molded Unshielded RF Coil
 2502-02G Molded Unshielded RF Coil
 2502-02H Molded Unshielded RF Coil
 2502-02J Molded Unshielded RF Coil
 2502-04F Molded Unshielded RF Coil
 2502-04G Molded Unshielded RF Coil
 2502-04H Molded Unshielded RF Coil
 2502-04J Molded Unshielded RF Coil
 2502-06F Molded Unshielded RF Coil

2502-06G Molded Unshielded RF Coil
2502-06H Molded Unshielded RF Coil
2502-06J Molded Unshielded RF Coil
2502-08F Molded Unshielded RF Coil
2502-08G Molded Unshielded RF Coil
2502-08H Molded Unshielded RF Coil
2502-08J Molded Unshielded RF Coil
2502-10F Molded Unshielded RF Coil
2502-10G Molded Unshielded RF Coil
2502-10H Molded Unshielded RF Coil
2502-10J Molded Unshielded RF Coil
2502-12F Molded Unshielded RF Coil
2502-12G Molded Unshielded RF Coil
2502-12H Molded Unshielded RF Coil
2502-12J Molded Unshielded RF Coil
2502-14F Molded Unshielded RF Coil
2502-14G Molded Unshielded RF Coil
2502-14H Molded Unshielded RF Coil
2502-14J Molded Unshielded RF Coil
2502-15F Molded Unshielded RF Coil
2502-15G Molded Unshielded RF Coil
2502-15H Molded Unshielded RF Coil
2502-15J Molded Unshielded RF Coil
2502-16F Molded Unshielded RF Coil
2502-16G Molded Unshielded RF Coil
2502-16H Molded Unshielded RF Coil
2502-16J Molded Unshielded RF Coil
2502-18F Molded Unshielded RF Coil
2502-18G Molded Unshielded RF Coil
2502-18H Molded Unshielded RF Coil
2502-18J Molded Unshielded RF Coil
2502-20F Molded Unshielded RF Coil
2502-20G Molded Unshielded RF Coil
2502-20H Molded Unshielded RF Coil
2502-20J Molded Unshielded RF Coil
2502-22F Molded Unshielded RF Coil
2502-22G Molded Unshielded RF Coil
2502-22H Molded Unshielded RF Coil
2502-22J Molded Unshielded RF Coil
2502-24F Molded Unshielded RF Coil
2502-24G Molded Unshielded RF Coil
2502-24H Molded Unshielded RF Coil
2502-24J Molded Unshielded RF Coil
2502-26F Molded Unshielded RF Coil
2502-26G Molded Unshielded RF Coil
2502-26H Molded Unshielded RF Coil
2502-26J Molded Unshielded RF Coil
2502-28F Molded Unshielded RF Coil
2502-28G Molded Unshielded RF Coil
2502-28H Molded Unshielded RF Coil

2502-28J Molded Unshielded RF Coil
2502-30F Molded Unshielded RF Coil
2502-30G Molded Unshielded RF Coil
2502-30H Molded Unshielded RF Coil
2502-30J Molded Unshielded RF Coil
2502-32F Molded Unshielded RF Coil
2502-32G Molded Unshielded RF Coil
2502-32H Molded Unshielded RF Coil
2502-32J Molded Unshielded RF Coil
2502-34F Molded Unshielded RF Coil
2502-34G Molded Unshielded RF Coil
2502-34H Molded Unshielded RF Coil
2502-34J Molded Unshielded RF Coil
2502-36F Molded Unshielded RF Coil
2502-36G Molded Unshielded RF Coil
2502-36H Molded Unshielded RF Coil
2502-36J Molded Unshielded RF Coil
2502-38F Molded Unshielded RF Coil
2502-38G Molded Unshielded RF Coil
2502-38H Molded Unshielded RF Coil
2502-38J Molded Unshielded RF Coil
2502-40F Molded Unshielded RF Coil
2502-40G Molded Unshielded RF Coil
2502-40H Molded Unshielded RF Coil
2502-40J Molded Unshielded RF Coil
2502-42F Molded Unshielded RF Coil
2502-42G Molded Unshielded RF Coil
2502-42H Molded Unshielded RF Coil
2502-42J Molded Unshielded RF Coil
2502-44F Molded Unshielded RF Coil
2502-44G Molded Unshielded RF Coil
2502-44H Molded Unshielded RF Coil
2502-44J Molded Unshielded RF Coil
2502-46F Molded Unshielded RF Coil
2502-46G Molded Unshielded RF Coil
2502-46H Molded Unshielded RF Coil
2502-46J Molded Unshielded RF Coil
2502-48F Molded Unshielded RF Coil
2502-48G Molded Unshielded RF Coil
2502-48H Molded Unshielded RF Coil
2502-48J Molded Unshielded RF Coil
2502-50F Molded Unshielded RF Coil
2502-50G Molded Unshielded RF Coil
2502-50H Molded Unshielded RF Coil
2502-50J Molded Unshielded RF Coil
2502-52F Molded Unshielded RF Coil
2502-52G Molded Unshielded RF Coil
2502-52H Molded Unshielded RF Coil
2502-52J Molded Unshielded RF Coil
2502-54F Molded Unshielded RF Coil

2502-54G Molded Unshielded RF Coil
2502-54H Molded Unshielded RF Coil
2502-54J Molded Unshielded RF Coil
2502-56F Molded Unshielded RF Coil
2502-56G Molded Unshielded RF Coil
2502-56H Molded Unshielded RF Coil
2502-56J Molded Unshielded RF Coil
2502-58F Molded Unshielded RF Coil
2502-58G Molded Unshielded RF Coil
2502-58H Molded Unshielded RF Coil
2502-58J Molded Unshielded RF Coil
2502-60F Molded Unshielded RF Coil
2502-60G Molded Unshielded RF Coil
2502-60H Molded Unshielded RF Coil
2502-60J Molded Unshielded RF Coil
2502-62F Molded Unshielded RF Coil
2502-62G Molded Unshielded RF Coil
2502-62H Molded Unshielded RF Coil
2502-62J Molded Unshielded RF Coil
2502-63F Molded Unshielded RF Coil
2502-63G Molded Unshielded RF Coil
2502-63H Molded Unshielded RF Coil
2502-63J Molded Unshielded RF Coil
2502-64F Molded Unshielded RF Coil
2502-64G Molded Unshielded RF Coil
2502-64H Molded Unshielded RF Coil
2502-64J Molded Unshielded RF Coil
2502-66F Molded Unshielded RF Coil
2502-66G Molded Unshielded RF Coil
2502-66H Molded Unshielded RF Coil
2502-66J Molded Unshielded RF Coil
2502-68F Molded Unshielded RF Coil
2502-68G Molded Unshielded RF Coil
2502-68H Molded Unshielded RF Coil
2502-68J Molded Unshielded RF Coil
2502-70F Molded Unshielded RF Coil
2502-70G Molded Unshielded RF Coil
2502-70H Molded Unshielded RF Coil
2502-70J Molded Unshielded RF Coil
2502-72F Molded Unshielded RF Coil
2502-72G Molded Unshielded RF Coil
2502-72H Molded Unshielded RF Coil
2502-72J Molded Unshielded RF Coil
2502-74F Molded Unshielded RF Coil
2502-74G Molded Unshielded RF Coil
2502-74H Molded Unshielded RF Coil
2502-74J Molded Unshielded RF Coil
2502-76F Molded Unshielded RF Coil
2502-76G Molded Unshielded RF Coil
2502-76H Molded Unshielded RF Coil

2502-76J Molded Unshielded RF Coil