




SEZ. A-A
(SECT. A-A)



SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

OBSOLETE	4	1-280359-0	7.62	10.6	12.2	2
	2	1-280358-0	2.54	5.6	7.1	
	22	280364-0	53.34	56.4	57.9	1
	15	280363-0	35.56	38.6	40.1	
	12	280514-0	27.94	31	32.5	
	10	280362-0	22.86	25.9	27.4	
	9	280512-0	20.32	23.3	24.9	
	8	280361-0	17.78	20.8	22.3	
	6	280360-0	12.70	15.7	17.3	
	4	280359-0	7.62	10.6	12.2	
	2	280358-0	2.54	5.6	7.1	
N° POS.	PART NUMBER		DIM. "A"	DIM. "B"	DIM. "C"	MATERIAL (SEE NOTE)

1 NORYL, UL94 V1, COLORE NERO

1 NORYL, UL94 V1, BLACK COLOUR

2 NORYL SE-1 COLORE ROSSO

2 NORYL SE-1 RED COLOUR

3 TOLLERANZA NON CUMULATIVA

3 NON CUMULATIVE TOLERANCE

4 PERMITTED FLASH 0.01 INCH MAX

CUSTOMER DRAWING
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION

TOLLERANZE, SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

± 0.3

ANGOLI
(ANGLES) ± 2°

DIS. 11 APRIL '95
(DR.) C. PIA

CONT. 11 APRIL '95
(CHK) R. CANTORE

DESCRIZIONE
(DESCRIPTION) AMPMODU II REC. HSG
SINGLE ROW, CRIMP ON-SNAP IN

LOC. SIZE NUMERO
(DWS NO)

REV.

FOGLIO
(SHEET)

I A3 C-280358

Y3

1 DI
(COP) 1

Y3	ADDED NOTE 4 AND OBSOLESCE OF PIN 1-280358-0 & 1-280359-0	SP	08NOV 2012
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. DATA (APP) (DATE)