






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code SEE NOTE 3				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
A	V12795	RDS	10/24/91		angles	.XX $\pm$.01/.3	scale 1:1
B	V20224	MRC	3/2/92		linear	.XXX $\pm$.005/.13	
C	V23049	SAR	7/24/92	0'±2'		.XXXX $\pm$.0020/.05	
D	V41077	GAH	7/6/94	dr	D.SHEAFFER	8/7/91	
E	V94441	JWS	12/30/99	enr	S.CLARK	10/24/91	dwg no
F	V05-0967	DAI	10/20/05	chr	S.CLARK	10/24/91	sheet 1 of 2 size
G	M06-0283	MHT	7/27/06	appd	S.CLARK	10/24/91	A3
sheet	revision	G	G				type
index	sheet	1	2				Product Customer Drawing


form: A3

PDM: Rev:G


STATUS: Released

Printed: May 13, 2011

PRODUCT NUMBER
SEE NOTE 1



SECTION U-U



SECTION X-X

NOTES:

- PRODUCT NUMBERING CODE:
50437-X YYX LF
LEAD FREE (OPTIONAL)
ALWAYS "X"
NO. OF POSITIONS SEE NOTE 2
ALWAYS "X"
BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6, 7, 8, 9,.....79, 80.
- MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC. FLAME RETARDANT PER UL94 V-0. COLOR: BLACK.
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.
- LENGTH FORMULAS
DIM A= .100/2.54 x NO. OF COLUMNS + .75/19.1
DIM B= .100/2.54 x NO. OF COLUMNS + .450/11.43
DIM C= .100/2.54 x NO. OF COLUMNS - .100/2.54
- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE OVEN.

mat'l. code SEE NOTE 3		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ec	no	dr	date	title
G					VERTICAL SHROUD 4 ROW W/O GUIDE PINS
					dwg no
					sheet 2 of 2 size
					50437 A3
					type
					Product Customer Drawing
sheet	revision				
index	sheet				