

Wiha Insulated Pliers and Cutters Sets


 1000volt

- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.

- In zipper carry case

32891 10 Piece Pliers & Screwdriver Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 volt. Individually Tested. [SHOP](#)

Item# 32891 Set Includes:	 lbs. 5.44
32818 - 8.0" Combination Pliers	32808 - 8.0" Long Nose
32838 - 8.0" Side Cutters	32848 - 6.75" Cable Cutters
32860 - 6.3" Universal Wire Stripper	
Insulated Phillips #1, #2, #3	Insulated Slotted 4.5, 6.5mm


 1000volt

- Pliers drop-forged from special tool steel, individually high frequency induction hardened, chrome and nickel plated, mirror-polished.

32889 8 Piece Pliers & Cutters Set. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E and CSA,  up to 1000 volt. Individually Tested. [SHOP](#)

Item# 32889 Set Includes:	 lbs. 4.53
32806 - 6.3" Long Nose Pliers	32808 - 8.0" Long Nose Pliers
32814 - 6.3" Lineman's Pliers	32832 - 6.3" Diagonal Cutters
32820 - 9.0" Lineman's Pliers	32838 - 8.0" High Lev. Cutters
32860 - 6.3" Wire Stripping Pliers	15000 - Electrician's Knife

Wiha Inomic 1000Volt Insulated Pliers

Insulation Standards:

EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA

Tools Meet 10,000 Volt Test Standards Rated to 1000 Volt ac or 1500 Volt dc


 1000volt

32850 Inomic Combo Pliers. Insulation According to EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  up to 1000 volt. Individually Tested. DIN ISO 5749 Precision machined forged head. Induction hardened for longest tool life. Cross hatched flat jaw & deep cut radius jaws for secure gripping of the work piece. Cutting edges are matched for precise cutting action. Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue. Palm side of grip has molded soft panel for added comfort in prolonged use. [SHOP](#)


Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32850	180	7.0	#6	1	.46

32852 Inomic Long Nose Pliers

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32852	160	6.3	#6	1	.43

32854 Inomic Diagonal Cutters

Item No.	mm	Inch	Cutting Capacity Copper AWG	Pkg.	lbs.
32854	160	6.3	#6	1	.41



Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue

Each tool includes a convenient jaw lock & handle return spring

Heads drop forged CV premium tool steel

Tools Meet 10,000 Volt Test Standards Rated to 1000 Volt ac or 1500 Volt dc

 1000V

32859 3 Pc. Insulated Inomic Pliers/Cutters Set Meets ASTM, EN/IEC, NFPA, CSA, ISO specifications. Award winning ergonomic design with head mounted at 23° angle to grip for reduced user fatigue. [SHOP](#)

Item# 32859 Set Includes:	 lbs. 1.45
32850 - Combo Pliers	32854 - Diagonal Cutters
32852 - Long Nose Pliers	91230 - Inomic Holster (Includes 3)



Three Holsters Included

[SHOP](#)

91230 Inomic Canvas Holster

Item No.	Width Size	Height Size	 lbs.	 pkg.
91230	4.0 x	4.5	.05	1

Holds any Inomic Pliers



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiha:

[91230](#) [32850](#) [32852](#) [32854](#) [32889](#) [32859](#) [32891](#)