

Ty-Fast®

TY400-50X



All-plastic cable tie for multi purpose use. UV-resistant version, especially recommended for outdoor applications.

T&B Catalog Number:

TY400-50X

EAN Number:

05414363064756

UPC Number:

78621089859

Description:

All-plastic, standard cable tie, 366 x 4.6 mm, black Polyamide 6.6 UV-resistant



Technical Information

Type	standard
Material	Polyamide 6.6 UV-resistant
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	black
Halogen free	yes
Silicone free	yes
UV-resistant	yes

Approvals

UL recognised	E49405
Germanischer Lloyd approval	yes
Lloyds Register approval	yes
MIL Spec.	MS-3367-2
Other approval	BVQ

Ordering Information

Length (mm)	366
Width (mm)	4.6
Max. Bundle Diameter (mm)	102
Min. Bundle Diameter (mm)	1.6
Min. Tensile Strength (N)	220
Quantity (pieces)	1000
Packaging Type	bag

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, ERG120, WT193A