





Straight Blade Devices
15 and 20 Ampere, 250 Volts
2 Pole, 3 Wire Grounding
Insulgrip® Plugs and Flanged Inlets




Plugs

15 and 20 Ampere

Description	Cord Diameter	Catalog Numbers	
Insulgrip® Plug, black and white nylon.	.230"-.720" (5.8-18.3)	HBL5666C	HBL5466C
Insulgrip® Plug, corrosion resistant, yellow nylon.	.230"-.720" (5.8-18.3)	HBL56CM66C	HBL54CM66C
8-Position Insulgrip® Angle Plug, black and white nylon.	.325"-.655" (8.3-16.6)	HBL5666CA	HBL5466CA
Valise® Plug, yellow nylon.	.220"-.660" (5.6-16.8)	HBL5666VY	HBL5464VY

Note: See page A-45 for accessories.



Insulgrip® Flanged Inlets

Description	Catalog Numbers	
Nylon casing, back wired.	HBL5678C	HBL5478C

*Notes: Flanged inlets are not HP rated.
See page A-45 for accessories.*