



GARDTEC

Part Number:

HP75 ("45" Plug)

Wire: **SPT1 2 and 3 conductor 105°C, 300 volts**

Lengths: **Standard** (12", 24", 36", 40",
48", 50", 60" and 80")

Custom (any length you desire.

When ordering, add desired length to
part number (i.e. 52.5" would be HP75-52.5))

Other options:

- **terminal connections** (any)
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **three conductor cords**
- **complete wire harness assemblies**
(rated at 105°C, 300 volts)
- **red tracer cords**
(all head configurations and lengths)



Listings:



UL listed (E189621, E156798)
Rated 10 AMP/125 VAC



CSA listed (LR76679-1)
Rated 7 AMP/125 VAC





GARDTEC

Part Number:

HP25 ("T" Plug)

Wire: **SPT1 2 and 3 conductor 105°C, 300 volts**

Lengths: **Standard** (12", 24", 36", 40",
48", 50", 60" and 80")

Custom (any length you desire.



When ordering, add desired length to
part number (i.e. 52.5" would be HP25-52.5))

Other options:

- **terminal connections** (any)
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **three conductor cords**
- **complete wire harness assemblies**
(rated at 105°C, 300 volts)
- **red tracer cords**
(all head configurations and lengths)

Listings:  **UL listed** (E189621, E156798)
Rated 10 AMP/125 VAC

 **CSA listed** (LR76679-1)
Rated 7 AMP/125 VAC





GARDTEC

Part Number:

SC60-W3


Material: **C1008 Steel**

Plating: **Bright Nickel Chrome**

(other plating styles are available upon request)

Ring Diameter: **1.6mm**

Rib Diameter: **1.6mm**





GARDTEC

Part Number:

SC60-W2


Material: **C1008 Steel**

Plating: **Bright Nickel Chrome**

(other plating styles are available upon request)

Ring Diameter: **1.6mm**

Rib Diameter: **1.6mm**






GARDTEC

Part Number:

SC80-Mxx

Media: **Polyurethane Foam UL94HF-1**
30/45/60/100PPI

Filter





GARDTEC


Part Number

SC60-P15/60


Material: *Plastic UL94V-0*

Media: *Polyurethane Foam UL94HF-1*
60PPI

Retainer



Filter



Guard

