

Status: **Active**

- Specifications
- Product Options
- Documentation & Tools
- Technical Support
- Contact Sales

CK505 clock, 56-pin Intel Yellow Cover part

- ## Features
- 2 - CPU differential low power push-pull pairs
 - 7- SRC differential low power push-pull pairs
 - 1 - CPU/SRC selectable differential low power push-pull pair
 - 1 - SRC/DOT selectable differential low power push-pull pair
 - 5 - PCI, 33MHz
 - 1 - PCI_F, 33MHz free running
 - 1 - USB, 48MHz
 - 1 - REF, 14.318MHz

CHIPSET MANUFACTURER	CHIPSET NAME	CLOCK SPEC.	CORE VOLTAGE (V)	INPUT FREQ (MHZ)	OUTPUTS (#)	PLATFORM NAME	POWER TYP (MW)	SPREAD SPECTRUM	XTAL FREQ (KHZ)
Intel	P43, X48, X38, Q35, P45, G41, Q43, B43, G45, G43, Q33, G35, Tiger Point, Eaglelake, Bearlake, Broadwater, NM10, P31, G33, G31, P35, Q45, 965	CK505	3.3	14.320000	19	Boulder Creek, McCreary, Salt Creek, Garlow, Bridge Creek, Pine Trail, Averill		Yes	14.320000

ORDERABLE PART ID	PART STATUS	PKG. CODE	PKG. TYPE	LEAD COUNT (#)	TEMP. GRADE	PB (LEAD) FREE	ORDER
9LP505-2HFLF	Active	PVG56	SSOP	56	C	Y	Check Inventory
9LP505-2HFLFT	Active	PVG56	SSOP	56	C	Y	Check Inventory
9LP505-2HGLF	Active	PAG56	TSSOP	56	C	Y	Check Inventory
9LP505-2HGLFT	Active	PAG56	TSSOP	56	C	Y	Check Inventory

	TITLE	TYPE ▲	FORMAT	FILE SIZE	DATE
	PC Clocks Contact Info	Misc	PDF	62 KB	05/29/2007

[GET TECHNICAL SUPPORT](#) ▶ [CONTACT SALES OFFICE](#) ▶