





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	FIBER TYPE
FLCDMC5BLY	50/125um MULTIMODE
FLCDMC6BLY	62.5/125um MULTIMODE
FLCDMC6E1Y	62.5/125um MULTIMODE
FLCDMCXAQY	50/125um OM3 MULTIMODE
FLCDSCBUY	9/125um SINGLEMODE

NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 50/125um, 62.5/125um, 50/125 OM3 MULTIMODE OR 9/125um SINGLEMODE 900um BUFFERED GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:
BODY/HARDWARE: PLASTIC
BOOT: THERMOPLASTIC RUBBER
FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN [] ARE METRIC [mm].



PART NUMBER		FLCDMC5BLY, FLCDMC6BLY, FLCDMC6E1Y, FLCDMCXAQY, FLCDSCBUY	
TITLE			
OPTICAM DUPLEX LC CONNECTOR WITH 900um BOOTS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01801YD/03	
DATASET FILE NAME		M01801YD_DC_DUP/03D	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
01801-33		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
MC	02-15-06	RTFI	NONE
SIZE			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	6/17/15	JSP	WJM	JGSW	A. REVISED DRAWING TITLE BLOCK.	01801-33