


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS

DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
597	A	RELEASED	JWM	3/2/01	JC	5/7/01	DJC	5/11/01



Size mm ²	AWG	Color Code W	SPC Type #	Dimensions (mm)					
				L-1	L-2	D-1	S-1	D-2	S-2
0.50	20	Orange	SPC4473	11.5	6	1.1	0.15	2.5	0.25
			SPC4474	13.5	8				
			SPC4475	15.5	10				
0.75	20	White	SPC4476	12.0	6	1.3	0.15	2.8	0.25
			SPC4477	14.0	8				
			SPC4478	16.0	10				
			SPC4479	18.0	12				
1.00	18	Yellow	SPC4480	12.5	6	1.5	0.15	3.0	0.3
			SPC4481	14.5	8				
			SPC4482	16.5	10				
			SPC4483	18.5	12				
1.50	16	Red	SPC4484*	12.5	6	1.8	0.15	3.4	0.3
			SPC4485	14.5	8				
			SPC4486	16.5	10				
			SPC4487	18.5	12				
			SPC4488	24.5	18				
2.50	14	Blue	SPC4489	15.0	8	2.3	0.15	4.2	0.3
			SPC4490	19.0	12				
			SPC4491	25.0	18				
4.00	12	Gray	SPC4492	17.5	10	2.9	0.2	4.8	0.3
			SPC4493	20.0	12				
			SPC4494	26.0	18				
6.00	10	Black	SPC4495	20.0	12	3.6	0.2	6.2	0.3
			SPC4496	25.0	18				
10.00	8	Ivory	SPC4497	21.0	12	4.6	0.2	7.5	0.3
			SPC4498	27.0	18				
16.00	6	Green	SPC4499	23.0	12	6.0	0.2	8.8	0.4
			SPC4500	29.0	18				
25.00	4	Brown	SPC4501	29.0	16	7.5	0.2	11.0	0.5
			SPC4502	31.0	18				
			SPC4503	35.0	22				

Size mm ²	AWG	Color Code DIN	SPC Type #	Dimensions (mm)					
				L-1	L-2	D-1	S-1	D-2	S-2
0.50	20	White	SPC4504	11.5	6	1.1	0.15	2.5	0.25
			SPC4505	13.5	8				
			SPC4506	15.5	10				
0.75	20	Gray	SPC4507	12.0	6	1.3	0.15	2.8	0.25
			SPC4508	14.0	8				
			SPC4509	16.0	10				
			SPC4510	18.0	12				
1.00	18	Red	SPC4511	12.5	6	1.5	0.15	3.0	0.3
			SPC4512	14.5	8				
			SPC4513	16.5	10				
			SPC4514	18.5	12				
1.50	16	Black	SPC4515*	12.5	6	1.8	0.15	3.4	0.3
			SPC4516	14.5	8				
			SPC4517	16.5	10				
			SPC4518	18.5	12				
			SPC4519	24.5	18				
2.50	14	Blue	SPC4520	15.0	8	2.3	0.15	4.2	0.3
			SPC4521	19.0	12				
			SPC4522	25.0	18				
4.00	12	Gray	SPC4523	17.5	10	2.9	0.2	4.8	0.3
			SPC4524	20.0	12				
			SPC4525	26.0	18				
6.00	10	Yellow	SPC4526	20.0	12	3.6	0.2	6.2	0.3
			SPC4527	25.0	18				
10.00	8	Red	SPC4528	21.0	12	4.6	0.2	7.5	0.3
			SPC4529	27.0	18				
16.00	6	Blue	SPC4530	23.0	12	6.0	0.2	8.8	0.4
			SPC4531	29.0	18				
25.00	4	Yellow	SPC4532	29.0	16	7.5	0.2	11.0	0.5
			SPC4533	31.0	18				
			SPC4534	35.0	22				

*Does not conform to DIN 46228 Part 4

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	3/2/01
CHECKED BY:	DATE:
JOHN COLE	5/7/01
APPROVED BY:	DATE:
Daniel Carey	5/11/01

DRAWING TITLE:

Insulated Wire Ferrules

SIZE DWG. NO.

A

TA-294

ELECTRONIC FILE

TA-294.dwg

REV

A

SCALE: NTS

U.O.M.: Millimeters

SHEET: 1 OF 1