

CMDZ2V4 THRU CMDZ47V

**SUPERmini™
ZENER DIODE
2.4 VOLTS THRU 47 VOLTS
250mW, 5% TOLERANCE**

SUPERmini™



SOD-323 CASE

**Central™
Semiconductor Corp.**

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMDZ2V4 Series Zener Diode is a high quality voltage regulator in an epoxy-molded SUPERmini™ package, designed for applications requiring low leakage.

MARKING CODE: See Marking Code on Electrical Characteristics table.

ABSOLUTE MAXIMUM RATINGS:

Power Dissipation (@T_A =50°C)
Operating and Storage Temperature

SYMBOL

P_D
T_J, T_{stg}

250
-65 to +175

UNIT

mW
°C

ELECTRICAL CHARACTERISTICS: (T_A=25°C), V_F=0.9 MAX @ I_F=10mA FOR ALL TYPES.

TYPE	ZENER VOLTAGE V _Z @ I _{ZT}			TEST CURRENT I _{ZT} mA	MAXIMUM ZENER IMPEDANCE Z _{ZT} @ I _{ZT} Ω	MAXIMUM REVERSE CURRENT I _R @ V _R		MARKING CODE
	MIN	NOM	MAX			I _R	@ V _R	
	VOLTS	VOLTS	VOLTS			μA	VOLTS	
CMDZ2V4	2.28	2.4	2.52	5.0	100	25	1.0	2V4
CMDZ2V6	2.47	2.6	2.73	5.0	100	25	1.0	2V6
CMDZ2V7	2.57	2.7	2.84	5.0	100	10	1.0	2V7
CMDZ3V0	2.85	3.0	3.15	5.0	95	5.0	1.0	3V0
CMDZ3V3	3.14	3.3	3.47	5.0	95	2.0	1.0	3V3
CMDZ3V6	3.42	3.6	3.78	5.0	90	2.0	1.0	3V6
CMDZ3V9	3.71	3.9	4.10	5.0	90	2.0	1.0	3V9
CMDZ4V3	4.09	4.3	4.52	5.0	90	1.0	1.0	4V3
CMDZ4V7	4.47	4.7	4.94	5.0	80	3.0	2.0	4V7
CMDZ5V1	4.85	5.1	5.36	5.0	60	2.0	2.0	5V1
CMDZ5V6	5.32	5.6	5.88	5.0	40	1.0	2.0	5V6
CMDZ6V2	5.89	6.2	6.51	5.0	10	3.0	4.0	6V2
CMDZ6V8	6.46	6.8	7.14	5.0	15	2.0	4.0	6V8
CMDZ7V5	7.12	7.5	7.88	5.0	15	1.0	5.0	7V5
CMDZ8V2	7.79	8.2	8.61	5.0	15	0.7	5.0	8V2
CMDZ9V1	8.65	9.1	9.56	5.0	15	0.5	6.0	9V1
CMDZ10V	9.50	10	10.50	5.0	20	0.2	7.0	10V
CMDZ11V	10.45	11	11.55	5.0	20	0.1	8.0	11V
CMDZ12V	11.40	12	12.60	5.0	25	0.1	8.0	12V
CMDZ13V	12.35	13	13.65	5.0	30	0.1	8.0	13V

R1 (31-October 2002)

ELECTRICAL CHARACTERISTICS (CONTINUED):

TYPE	ZENER VOLTAGE V _Z @ I _{ZT}			TEST CURRENT	MAXIMUM ZENER IMPEDANCE	MAXIMUM REVERSE CURRENT		MARKING CODE
	MIN	NOM	MAX	I _{ZT}	Z _{ZT} @ I _{ZT}	I _R @ V _R		
	VOLTS	VOLTS	VOLTS	mA	Ω	μA	VOLTS	
CMDZ15V	14.25	15	15.75	5.0	30	0.05	10.5	15V
CMDZ16V	15.20	16	16.80	5.0	40	0.05	11.2	16V
CMDZ18V	17.10	18	18.90	5.0	45	0.05	12.6	18V
CMDZ20V	19.00	20	21.00	5.0	55	0.05	14.0	20V
CMDZ22V	20.90	22	23.10	5.0	55	0.05	15.4	22V
CMDZ24V	22.80	24	25.20	5.0	70	0.05	16.8	24V
CMDZ27V	25.65	27	28.35	5.0	80	0.05	18.9	27V
CMDZ30V	28.50	30	31.50	5.0	80	0.05	21.0	30V
CMDZ33V	31.35	33	34.65	5.0	80	0.05	23.1	33V
CMDZ36V	34.20	36	37.80	5.0	90	0.05	25.2	36V
CMDZ39V	37.05	39	40.95	5.0	130	0.05	27.3	39V
CMDZ43V	40.85	43	45.15	5.0	150	0.05	30.1	43V
CMDZ47V	44.65	47	49.35	5.0	180	0.05	32.9	47V

SOD-323 CASE - MECHANICAL OUTLINE

