

Search within category

GO

BUY NOW

DESIGN / INSTALL



PUFR6X04BU-UG

Shielded copper cable, category 6A U/FTP, riser (CMR), 4-pair, conductors are 23 AWG with HDPE insulation, twisted in pairs, each individual twisted pair includes a metallic foil shield and is protected by a low smoke, flame-retardant PVC jacket, blue.

Available in North and Latin America

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Color	Blue			
AWG Size	23			
Length (ft.)	1000			
Length (m)	305			
Nominal Diameter (In.)	0.31			
Nominal Diameter (mm)	7.87			
Jacket Material	Polyvinyl chloride			
No. of Pairs	4			
Packaging Type	Reel			
Application	Indoor			
Cable Type	U/FTP			
Flammability Rating	Riser (CMR)			
Installation Temperature	0°C to 60°C (32°F to 140°F)			
Insulation Diameter (In.)	0.053-0.059			
Insulation Diameter (mm)	1.35-1.50			
Note	Available in North and Latin America			
Operating Temperature	-20°C to 60°C (-4°F to 140°F)			
Part Features	Third party tested, Additional feature and benefit, Cross-divider, Reduced attenuation, Easy payout carton, Tested beyond the standards and Descending length cable markings.			
Performance Level	Category 6A			
Sub Brand	PanNet			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	5,000			