


LOC	DIST	REVISIONS				
BD	0	P	LTR	DESCRIPTION	DATE	APVD
			G3	REVISED PER ECO-11-004587	11MAR11	RK HMR



- 1 PARTS PACKAGED UNASSEMBLED.
- △2 CABLE CLAMPING AREA ADJUSTABLE FROM .261 TO .517 SQ IN BY CHANGING CLAMPING INSERT.
- 3 1.125 MAXIMUM CABLE OUTSIDE DIAMETER.
- △4 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 75 ONLY.
- △5 FINISH: ZINC NON-HEXAVALENT CHROMATE.
- △6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△5	△4 BULK	206512-6
	INDIVIDUAL	206512-5
△5	SMALL PACK	206512-4
△5	SMALL PACK	206512-3
△5	△4 BULK	206512-2
△5	INDIVIDUAL	206512-1
SCREW FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

MATERIAL

THERMOPLASTIC

DWN
A GRAFF
CHK
W.G.LENKER
APVD
-
PRODUCT SPEC
108-10024
APPLICATION SPEC
-
WEIGHT
-

4/29/91
7-23-92
-

TE Connectivity

CABLE CLAMP KIT, LARGE,
SHELL SIZE 23, CPC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-206512

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
G3