


NOTES:

1. BRAIDED STRAP IS #4 AWG STRANDED COPPER, TIN PLATED
FERRULES ARE TIN PLATED COPPER.
2. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
3. PARTS ARE UL LISTED AND CSA CERTIFIED FOR BONDING
APPLICATIONS ONLY.



PANDUIT PART NUMBER	BRAIDED STRAP SIZE	INSULATION	NO. OF BRAIDS IN FERRULE	DIMENSIONS - IN [mm]							
				L	D	S	W	C	T	H DIA	FERRULE LENGTH
BS201246EU	4 AWG	NO	1	12.00 [304.8]	10.75 [273.1]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS201846EU	4 AWG	NO	1	18.00 [457.2]	16.75 [425.5]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]
BS202446EU	4 AWG	NO	1	24.00 [609.6]	22.75 [577.9]	1.25 [31.8]	1.06 [27.0]	.63 [15.9]	0.13 [3.3]	0.44 [11.2]	2.50 [36.5]

[illegible]