

Specifications

- * Due to ongoing technological advances, consult factory for certification specifics.

15/32-32UNS-2A
THREAD

.687[17.44]

.465[11.81]









.778[19.76]

.422[10.72]

1.308[33.22]

KEYWAY
.072[1.82]
X
.038[.965] DP

.750[19.05]

		
SOLDER LUG	.250 TAB (Q.C.)	.187 TAB (Q.C.)
TERMINAL TYPE		
		
SCREW (ASSEMBLED)	WIRE LEAD	PRINTED CIRCUIT
		
MOUNTING HOLE	WITH KEYWAY	WITH LOCKING RING

FUNCTION	LUG	(QC)	(QC)	TERM.	LEAD	TERM.
ON-NONE-OFF	0	1	3	4	5	6
(ON)-NONE-OFF	A	B	D	E	F	G
ON-NONE-(OFF)	L	M	R	S	T	U
ON-NONE-ON	0	1	3	4	5	6
ON-NONE-(ON)	A	B	D	E	F	G
ON-OFF-ON	0	1	3	4	5	6
ON-OFF-(ON)	A	B	D	E	F	G
(ON)-OFF-(ON)	L	M	R	S	T	U

	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
BAT	.406	.343	52	57
	.562	.465	63	68
	.687	.465	73	78
	1.00	.465	A3	A8
	1.25	.465	B3	B8
	.687	.465	NBL3	NBL8
	.687	.465	NWH3	NWH8
	1.50	.465	C3	C8

3 NBL toggle uses black oxide plated metal bushing for standard construction. NWH toggles use nickel plated metal bushing for standard construction.

15/32-32UNS-2A
THREAD

.687[17.44]

.379[9.63]

.865[21.97]

.422[10.72]

1.375[34.92]

KEYWAY
.072[1.82]
X
.038[.965] DP

.750[19.05]

B	BLACK
W	WHITE

53