




4.06 MAX OR (2) 3.30 DIA [.160 MAX OR (2).130 MAX]	[#16-#12] AWG	0.81 [.032]	42663-2
INSUL RANGE	WIRE SIZE	MATING TAB THK ±0.025 [.001]	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 2/15/94	TE Connectivity	
		CHK MS FEHER 2/15/94		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J GILLESPIE 2/15/94	NAME RECEPTACLE, FASTIN-FASTON, 7.92 [.312] SERIES	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		
MATERIAL BRASS	FINISH TIN	SIZE A300779		DRAWING NO C-42663
		CUSTOMER DRAWING		RESTRICTED TO —
		SCALE 4:1	SHEET 1 of 1	REV J