







N= NUMBER OF CONTACTS



Material
Terminal body
(contact pin): Brass(CuZn) Tin plated
Insulator (housing): Thermoplastic (UL94V-0),Green

Electrical cULus/CSA/VDE

Voltage rating: 300VAC/300VAC/300VAC

Current rating: 20A/20A/20A

Wire range:

Solid wire(AWG):

Stranded wire(AWG):

Withstanding Voltage: 1.6KV/2.5KV/2.5KV

Operating temperature: -30°C to +105°C

Soldering temperature: 250°C±10°C/5 Sec

Safety Approval:



RoHS compliant

Unit: mm



File No.: E349947

Scale	1:1					Date	Name	Customer-No.		G	
TOLERANCE						Drawn	10.12.2009	Dean			
X.	±0.50					Approved	18.04.2016	Joanna	ASSMANN WSW-No.		
X.X	±0.30								A-TB500-OQxxCV		
X.XX	±0.10										
DIM	TOL	②	Add UL	18.04.2016	Joanna				Drawing-No.		H
X.°	±1°		①	Drawn	10.12.2009				Dean	ASS 3861 CO	
Angle	TOL	Id.		Modification	Date	Name	Replace	Sheet			