



Main

Range of product	Zelio Relay
Product or component type	Socket
Contact terminal arrangement	Separate
Product compatibility	Relay RXM4....
Device short name	RXZ
Sale per indivisible quantity	10

Complementary


[Ith] conventional free air thermal current	10 A 5 A with bus jumper
[Ue] rated operational voltage	< 250 V
Tightening torque	<= 1 N.m (M3 screw(s))
Fixing mode	By screw mounting on panel Clip-on mounting on 35 mm symmetrical DIN rail
Marking	CE
Width	27 mm
Product weight	0.058 kg 0.07 kg

Environment

Connections - terminals	Connector, flexible cable with cable end 1 x 0.25...1 x 2.5 mm ² /AWG22...AWG14 Connector, flexible cable with cable end 2 x 0.25...2 x 1 mm ² /AWG22...AWG17 Connector, solid cable without cable end 1 x 0.5...1 x 2.5 mm ² /AWG20...AWG14 Connector, solid cable without cable end 2 x 0.5...2 x 1.5 mm ² /AWG20...AWG16
Standards	IEC 61984
Product certifications	CSA UL
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-40...55 °C
IP degree of protection	IP20 conforming to EN/IEC 60529
Dielectric strength	2500 V
RoHS EUR status	Compliant
RoHS EUR conformity date	0801

Socket

Socket with Separate Contact Terminals and Connector for 4 Timed C/O Contacts



- 1 Relay
- 2 Protection Module
- 3 Carriage Stirrup
- 5 2 Links connection