

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191540047](#)
Status: **Active**
Description: Step Down Butt Splice for 6-8 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification \(PDF\)](#)

General
Product Family Splices
Series [19154](#)
Comments Step down: 6 to 8 AWG
Mil-Spec N/A
Product Name Butt - Step Down

Physical
Barrel Type Closed - Brazed
Color - Resin Natural
Insulation PVC
Material - Resin PVC
Packaging Type Bag
Temperature Range - Operating -40°C to +105°C
Wire Insulation Diameter 11.05mm (.435") max
Wire Size AWG 6, 8

Electrical
Voltage - Maximum 600V

Material Info
Old Part Number ED-662X

Reference - Drawing Numbers
Sales Drawing CD21001




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19154Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Putt Pump Dieless Head System	0192860065
Die Set (large) for the HHLS Hydraulic Crimper	0192890004
Hand Crimp Tool	0640013900
Manual Putt Pump Hydraulic System, Die set required	0192860117

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION