


EVEREADY SILVER NO. R6**AA****Zinc Chloride****Industry Standard Dimensions**

(millimeters)

**Specifications****Chemical System:** Zinc-Manganese Dioxide (Zn/MnO₂)

(no added mercury or cadmium)


Designation: IEC-R6**Nominal Voltage:** 1.5 volts**Typical Capacity:** 1,100 mAh* (to 0.8 volts)

(based on 25 mA continuous at 21°C)


* Varies according to the applied load, temperature, and cutoff voltage.

Operating Temp: -18°C to 55°C**Typical Weight:** 15 grams**Typical Volume:** 8.0 cubic centimeters**Jacket:** Metal**Storage / Capacity Characteristics**


Effects of Storage at Various Temperatures

**Industry Standard Tests (21°C)****REMOTE**


24 ohm 15 sec/min, 8 hrs/day

**TAPE PLAYER**


10 ohm 1 hr/day

**TOY**

3.9 ohm 1 hr/day

**PHOTOFLASH**

1.8 ohm 15 sec/min

**Important Notice**

This data sheet contains typical information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

©Eveready Battery Company, Inc. - All Rights Reserved